



Dimensions: mm (In.)



Switch Function

POS.1	POS.2	POS.3
MOM	OFF	MOM
2-3, 5-6, 8-9	OPEN	2-1, 5-4, 8-7
<p>2 Comm. 1 3</p> <p>4 5 Comm. 6</p> <p>7 8 Comm. 9</p>		<p>2 Comm. 1 3</p> <p>4 5 Comm. 6</p> <p>7 8 Comm. 9</p>

P.C. Mounting



Mechanical Specifications:

- Mechanical Life: 30,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

Electrical Specifications:

- Rating: 2A / 250VAC, 5A / 120 VAC or 28 VDC
- Contact Resistance: 10mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Dielectric Strength: 1,000 V RMS@sea level

Note:

- RoHS Compliant by Exemption

Sealed Miniature Toggle Switch  
108-1A34T1605-EVX



Available from Mouser Electronics

www.mouser.com

1-800-346-6873