



a vital part of your world

Find Answers:

Monday, 14 November,

**CATALOG**

- [Cross Reference](#)
- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

---

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

[Home](#)

e-bulletin newsletter  
**SUBSCRIBE NOW!**  
click here

**CPC (Circular Plastic) & Metal-Shell CPC Connectors**

↳ **CPC Connectors**

**AMP** 207216-2 Active

Not ELV or RoHS Compliant

**(Corporate P/N: 207216-2)**

[Search for Compliant \(RoHS/ELV\) Alternates](#)

[CAD Geometry](#) | [Search for Parts](#)

Product Documentation - Please use the customer drawing for all design activity.	
<a href="#">Customer Drawing</a>	<a href="#">Drawings &amp; Specifications</a>
<a href="#">View Customer Drawing(s).</a>	<a href="#">View All Documents.</a>

Related Part Information		
<a href="#">General Information</a>	<a href="#">eCommerce</a>	<a href="#">Related Part Information</a>
<ul style="list-style-type: none"> <li>➤ <a href="#">General Info</a></li> <li>➤ <a href="#">Sales Info</a></li> <li>➤ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Pricing &amp; Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Tooling</a></li> </ul>

**Photos & Line Drawings** - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

[Contact Arrangement](#)

**Searchable Features:**

**Other Properties:**

- Brand:** AMP
- [RoHS/ELV Compliance:](#)** Not ELV/RoHS compliant
- [Lead Free Solder Processes:](#)** Wave solder capable to 240°C, Wave solder capable to 265°C
- [Product Type:](#)** Connector
- [Number of Positions:](#)** 28
- [Gender:](#)** Receptacle
- [Pin/Socket:](#)** Socket
- [Preloaded:](#)** Yes
- [Terminate To:](#)** Printed Circuit Board
- [Shell Size:](#)** 17
- [Shell Type:](#)** All Plastic
- [Shell Thread Size:](#)** 15/16-20 UNEF-2A
- [Product Series:](#)** Series 2
- [Reverse Numbering:](#)** No
- [Mount Style:](#)** Mounting Holes
- [Sealed:](#)** No

- [Panel Attachment Method:](#)** Square Flange
- [Housing Material:](#)** Thermoplastic
- [Housing Color:](#)** Black
- [Housing Material Flammability Rating:](#)** UL 94V-0
- [Termination Post Length \(mm \[in\]\):](#)** 10.20 [0.402]

<a href="#">VDE Tested:</a>	No
<a href="#">Contact Mating Area Plating:</a>	Gold (30) over Nickel (50)
<a href="#">Contact Termination Area Plating:</a>	Tin Lead over Nickel
<a href="#">Standard or Reverse Gender:</a>	Reverse

[Copyright and Privacy Statement](#)  
Visit [Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]