

CATALOG
Cross Reference

[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

CPC (Circular Plastic) & Metal-Shell CPC Connectors
↳ CPC Connectors


207369-1

[Active](#)

[Not ELV or RoHS Compliant](#)
(Corporate P/N: 207369-1)
[Search for Compliant \(RoHS/ELV\)](#)
[Alternates](#)
[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ↳ General Info ↳ Sales Info ↳ Assembly Subcontractors 	<ul style="list-style-type: none"> ↳ Pricing & Availability 	<ul style="list-style-type: none"> ↳ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)
[Contact Arrangement](#)
Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Connector
Number of Positions:	28
Gender:	Receptacle
Pin/Socket:	Pin
Preloaded:	Yes
Terminate To:	Printed Circuit Board
Shell Size:	17

Other Properties:

Panel Attachment Method:	Square Flange
Mounting Hole Diameter (mm [in]):	3.81 [.150]
Housing Material:	Thermoplastic
Housing Color:	Black
Housing Material Flammability Rating:	UL 94V-0
Contact Type:	Posted
Recommended Hole Size (mm [in]):	1.19 [0.047]
Termination Post Length (mm [in]):	3.18 [0.125]
Comment:	Posts are 0.43 [.017] offset from centerline of contacts.

<u>Shell Type:</u>	All Plastic
<u>Shell Thread Size:</u>	5/8 - 24 UNEF-2A
<u>Product Series:</u>	Series 2
<u>Reverse Numbering:</u>	No
<u>Mount Style:</u>	Mounting Holes
<u>Sealed:</u>	No
<u>VDE Tested:</u>	No
<u>Contact Mating Area Plating:</u>	Gold (30) over Nickel (50)
<u>Contact Termination Area Plating:</u>	Tin Lead over Nickel
<u>Standard or Reverse Gender:</u>	Standard

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]

.