

- Replacement for 35W PAR16 halogen lamp
- Up to 85% energy saving
- Dimmable
- Lifetime of 35,000 hrs
- Suitable replacement for halogen or incandescent spots. Perfectly highlights the corridors, stairwells,



Order Code 52045

General Data

Lamp Socket GU10

Design Lens

Geometric Data

Length (mm) 58

Diameter (mm) 50

Weight (g) 50

Electric Data

Wattage (W) 6.5

Voltage (V) 220-240

Power Factor ≥ 0.90

Operating Frequency (Hz) 50-60

Photometric Data

Luminous Flux (lm) 240

CRI ≥ 80

CCT (K) 2700 – warm white

Luminous Intensity (cd) 580

Beam Angle (°) 35

Lifetime (hrs) 35,000

Switching cycle 18,000

Wattage Equivalent (W) 35





Order Code	52045
Product Description	LED PAR16 GU10 6.5W 2700K WW 240LM DIM Box

Technical Packaging Details

Barcode	023942520450
EAN 128	(02)00023942520450(37)40(91)162
EAN 14	50023942520455
Pack Dimensions (HxWxL)	62 mm x 50 mm x 50 mm
Pack Weight	77 g
Carton Qty (Shipping Unit)	10
Carton Dimensions (HxWxL)	330 mm x 300 mm x 150 mm
Cartons/Layer	51
Layers/Pallet	6
Units/Pallet	2040

Photometric Diagram

52045

