



Electronics

a vital part of your world

Find Answers:

Tuesday, 15 November, 2005

CATALOG

- Cross Reference
 - Competitive Products
 - Military Spec P/Ns
 - Tyco Brand P/Ns

- Part Number Search
- Document Search
- Product Type Search
- Product Family Search
- Alphabetical Search
- RoHS/ELV Compliance & Alternates
- CAD Model Search
- Brand Search
- Tool Search
- Multiple Part Comparison
- Lead Free Solutions
- Help/Glossary

Home

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

CPC (Circular Plastic) & Metal-Shell CPC Connectors

↳ CPC Connectors

AMP 206038-4 Active

Directive 2002/95/EC Compliant

RoHS Compliant

(Tyco Electronics P/N: 206038-4)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> General Info Sales Info Assembly Subcontractors 	<ul style="list-style-type: none"> Pricing Product Availability 	<ul style="list-style-type: none"> Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

Product Photo	Contact Arrangement
-------------------------------	-------------------------------------

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Connector
Number of Positions:	28
Gender:	Receptacle
Used With:	Socket Contacts
Preloaded:	No
Terminate To:	Wire
Shell Size:	17
Shell Type:	All Plastic
Shell Thread Size:	15/16-20 UNEF-2A

Other Properties:	
RoHS/ELV Compliance History:	Always was RoHS compliant
Wire Insulation Diameter (mm [in]):	1.73 [0.068]
Panel Attachment Method:	Square Flange
Mounting Hole Thread Size:	4-40
Housing Material:	Thermoplastic
Housing Color:	Black
Housing Material Flammability Rating:	UL 94V-0
Insert Material:	Brass

Product Series:	Series 2
Reverse Numbering:	No
Mount Style:	Panel
Sealed:	No
VDE Tested:	No
Standard or Reverse Gender:	Reverse

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]