


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000040](#)
Status: **Active**
Overview: [Mini-Fit Jr. Power Connectors](#)
Description: Mini-Fit Male Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass Contact, 18-24 AWG, Reel

Documents:

Drawing (PDF)	Product Specification TS-5556-002-001 (PDF)
Drawing (PDF)	Packaging Specification PK-5558-001 (PDF)
Product Specification PS-5556-001-001 (PDF)	Test Summary 55560000-TS-000 (PDF)
Product Specification PS-5556-002-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Terminals
Series	5558
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr. Power Connectors
Packaging Alternative	39-00-0041 (Loose)
Product Name	Mini-Fit
UPC	800753643239

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.123/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	5558T
--------------------	-------

Reference - Drawing Numbers

Packaging Specification	PK-5558-001
Product Specification	PS-5556-001-001, PS-5556-002-001, TS-5556-002-001
Sales Drawing	SD-5558****
Test Summary	55560000-TS-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

[China RoHS](#)

Green Image

Compliant

Not Contained

Search Parts in this Series

[5558](#) Series

Mates With

[5556](#) Mini-Fit Crimp Terminal

Use With

[5559](#) Mini-Fit Jr. Plug Housing, [30068](#) Mini-Fit TPA Plug Housing, [42475](#) Mini-Fit BMI Plug Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool	11030044
Hand Crimp Tool for Mini-Fit Jr. Male and Female Crimp Terminals, 18-24 AWG	638190901

FineAdjust Applicator 639002600
 for Insulation OD
 2.50-2.95mm, 18-24
 AWG Wire
 FineAdjust Applicator 639002900
 for Insulation OD
 1.65-2.05mm, 18-24
 AWG Wire
 FineAdjust Applicator 639015600
 for Insulation OD
 1.90-2.30mm - 18-24
 AWG
 FineAdjust Applicator 639023900
 for Insulation OD
 1.40-1.70mm - 18-24
 AWG
 FineAdjust Applicator 639024800
 for Insulation OD
 2.50-2.95mm
 Optimized for 18
 AWG Only
 FineAdjust Applicator 639024900
 for Insulation OD
 2.30-2.60mm - 18-24
 AWG
 T2 Terminator 639102600
 for Insulation OD
 2.50-2.95mm, 18-24
 AWG
 T2 Terminator for 639102900
 Insulation OD 1.65
 – 2.05mm, 18–24
 AWG
 T2 Terminator 639115600
 for insulation OD
 1.90-2.30mm - 18-24
 AWG
 T2 Terminator 639123900
 for insulation OD
 1.40-1.70mm - 18-24
 AWG
 T2 Terminator 639124800
 for insulation OD
 2.50-2.95mm
 optimized for 18
 AWG only
 T2 Terminator 639124900
 for insulation OD
 2.30-2.60mm - 18-24
 AWG

Japan

Description	Product #
S-1 Applicator for Mini-Fit Plug and Receptacle Terminals, 18-24 AWG, UL1007 Wires	<u>570223700</u>
S-1 Applicator for Mini-Fit Plug and Receptacle Terminals, 18-24 AWG, UL1015 Wires	<u>570223710</u>
Hand Extraction Tool	<u>570316000</u>

This document was generated on 11/23/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION