


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [58721-0010](#)
Status: **Active**
Overview: [Heavy Duty Rectangular Connectors - HMC™](#)
Description: HMC™ Rectangular Industrial Hood Bracket, Multi-Module Type, 48-72 Circuits, Type A Polarization

Documents:

3D Model	Product Specification PS-58719-006 (PDF)
Drawing (PDF)	Application Specification AS-58723-004 (PDF)
Product Specification PS-58719-005 (PDF)	RoHS Certificate of Compliance (PDF)



Agency Certification

TUV R72081037

General

Product Family	I/O Connectors
Series	58721
Application	Panel-Mount
Component Type	Hood Bracket
Overview	Heavy Duty Rectangular Connectors - HMC™
Product Name	HMC™
Type	N/A
UPC	800753921023

Physical

Circuits (Loaded)	48
Circuits (maximum)	48
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Net Weight	46221.300/mg
Orientation	Vertical
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	N/A
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP65

Electrical

Current - Maximum per Contact	12A, 20A
Voltage - Maximum	250V AC

Material Info

Reference - Drawing Numbers

Application Specification	AS-58723-004
Product Specification	PS-58719-005, PS-58719-006, RPS-58719-003, RPS-58719-004, RPS-58719-006, RPS-58719-007, RPS-58719-008
Sales Drawing	SD-58721-002

EU RoHS ELV and RoHS Compliant REACH SVHC Not Reviewed Low-Halogen Status Not Reviewed	China RoHS
--	-----------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[58721Series](#)

Mates With

[58719-0010](#) Panel Mount Bracket

Use With

[51194](#) Housing, [51195](#) Housing, [58723-0010](#) Hood, [51203](#) Housing, [51204](#) Housing