


## Model 5931 Panel Mount IEC 1010 4mm Banana Jack For Sheathed Plugs



Recommended Maximum Panel Thickness: .28" (7mm)

### FEATURES:

- Banana jack mates to Pomona's models 5907A, 5908A & 5909A flexible sheathed style of DMM test leads.
- Slip ring threads onto the insulated body to firmly secure jack to panel.
- Banana jack is gold plated for superb electrical connection.

### MATERIALS:

Banana Jack: Brass, Gold Plated

Insulation: Nylon

Locking Ring: Brass, Nickel Plated

### RATING:

Operating Voltage: 1000 VRMS Max.

Current: 36 Amperes Max.

### ORDERING INFORMATION: Model 5931-\*

\* = Color, Std. Colors: -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White

Sold in packs of ten.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA