

TECHNICAL CHARACTERISTICS



MATERIAL
 INSULATOR: PBT
 COLOR: WHITE
 CONTACT MATERIAL: COPPER ALLOY
 CONTACT TYPE: STAMPED
 CONTACT PLATING: SELECTIVE GOLD
 SHIELDING: BRASS NI PLATED
 QUALITY CLASS: 1500 MATING CYCLES

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 105°C
 FLAMABILITY RATING: UL94-V0
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 1A
 WORKING VOLTAGE: 30V AC
 INSULATOR RESISTANCE: >1000 MOHM
 DIELECTRIC WITHSTANDING VOLTAGE: 750V AC/MN
 CONTACT RESISTANCE: 20 mOHM MAX

SOLDERING
 WAVE PROCESS ONLY


PACKAGING
 TRAY



RoHS Compliant

G	06-MAY-09	UPDATE	JC
F	05-DEC-07	MODIFICATIONS	EC
E	02-MAR-07	UPDATE	EC
D	01-FEB-07	DRAW	EC
C	10-JAN-06	LEAD FREE	JP
B	29-MAR-04	PDF	JP
A	31-JAN-01	DRAW	PEARL
REV	DATE	FILE	BY

PROJECTION:



APPROVAL: RJ

GENERAL TOLERANCE

.X = +/- 0.2
 .XX = +/- 0.15

UNIT: MM

SCALE:

SHEET: 1/1

DRAW: PEARL



DESCRIPTION: USB FEMALE R/A A TYPE

WERI PART NO: 61400416021

SIZE

A4