


C0402C470K8GACTU

aka C0402C470K8GAC7867

Capacitor, ceramic, 47 pF, +/-10% Tol, 10V, C0G, 0402



Dimensions (mm)

Specifications

ID	Dimension	Tolerance	Manufacturer:	KEMET
L	1.00	+/-0.05	Capacitance:	47 pF
W	0.50	+/-0.05	Chip Size:	0402
T	0.5	+/-0.05	Voltage:	10V
B	0.30	+/-0.1	Temperature Coefficient:	C0G
S	0.3	min	Tolerance:	+/-10%
			Application:	Std Chip
			Termination Type:	Tin
			Marked:	No
			Dissipation Factor:	0.1%
			Insulation Resistance:	100 GOhm
			Dielectric Strength:	25V
			Package Kind:	T&R
			Package Size:	7in
			Package Type:	Paper Tape
			Package Quantity:	10000