


# C0603C152K4RACTU

aka C0603C152K4RAC7867

Capacitor, ceramic, 1500 pF, +/-10% Tol, 16V, X7R, 0603



## Dimensions (mm)

## Specifications

ID	Dimension	Tolerance
L	1.60	+/-0.15
W	0.80	+/-0.15
T	0.8	+/-0.07
B	.35	+/-0.15
S	0.7	min

<b>Manufacturer:</b>	KEMET
<b>Capacitance:</b>	1500 pF
<b>Chip Size:</b>	0603
<b>Voltage:</b>	16V
<b>Temperature Coefficient:</b>	X7R
<b>Tolerance:</b>	+/-10%
<b>Application:</b>	Std Chip
<b>Termination Type:</b>	Tin
<b>Marked:</b>	No
<b>Dissipation Factor:</b>	3.5%
<b>Insulation Resistance:</b>	100 GOhm
<b>Dielectric Strength:</b>	40V
<b>Package Kind:</b>	T&R
<b>Package Size:</b>	7in
<b>Package Type:</b>	Paper Tape
<b>Package Quantity:</b>	4000