


Capacitor, film, 380 uF, 10% Tol, 400V@85C, Lead Spacing=45mm



**Dimensions (mm)**

**Specifications**

ID	Dimension	Tolerance
D	84	+/-0.5
L	64	+/-2
S	45	+/-1
LL	20	nom
F	10	nom

<b>Manufacturer:</b>	KEMET
<b>Brand:</b>	Arcotronics
<b>Application:</b>	Power Electronic
<b>Capacitance:</b>	380 uF
<b>Tolerance:</b>	10%
<b>Temperature Range:</b>	-40/+85C
<b>Climate Category:</b>	40/85/56
<b>Voltage DC @ 85C:</b>	400V
<b>Dielectric:</b>	Metallized Polypropylene
<b>Construction:</b>	Non Inductive
<b>Maximum dVdT:</b>	15v/s
<b>Body Type:</b>	Vertical Can Standard Profile
<b>Package Kind:</b>	Bulk