

CBT25J220R Product Details

 [Live Product Chat](#)



Fixed Resistors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Resistor Type = Power Resistor
- Resistance Selection = <1K ?
- Resistance = 220 ?
- Power Rating = .25 W
- Tolerance = 5 %

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

CBT25J220R
(1-1625875-9)

TE Internal Number: 1-1625875-9

 [Active](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Resistor Type = Power Resistor
- [Resistance \(?\)](#) = 220
- [Element](#) = Carbon Composition
- [Termination Type](#) = Tinned Copper Leads

Electrical Characteristics:

- [Resistance Selection \(?\)](#) = <1K
- [Power Rating \(W\)](#) = 0.25
- [Tolerance \(%\)](#) = 5
- [Package Type](#) = Ammo Packed

Body Related Features:

- [Series](#) = CBT
- [Mount Style](#) = Axial Leaded
- [Package, Component Size](#) = 6.3 x 2.4

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Temperature Coefficient \(ppm/°C\)](#) = -700 to +400

Operation/Application:

- [Application](#) = High Voltage

Other:

- Brand = Neohm

[Provide Website Feedback](#) | [Need Help?](#)