


MAB-03A-T-D1




- Digital Output Microphone
- Surface Mount Electret Design
- Omni-directional
- Very Small Size

Specifications:

Sensitivity	-28 ± 3 dB
Max. Input SPL	120 dB
Operating Voltage	1.64-2.86 V
Current Consumption	500 μA (max)
S/N Ratio	55 dB (min)
Directivity	Omni
Operation Temp.	-30°C to +70°C
External Size	3 x 4 x 1mm
Mass	<0.5 g

Frequency Response



Sound hole

