


GNM314R71C473MA01#

" # " indicates a package specification code.



< List of part numbers with package codes >
 GNM314R71C473MA01L , GNM314R71C473MA01K , GNM314R71C473MA01B

Shape



References

Packaging	Specifications	Minimum quantity
L	Embossed tape (180mm)	3000
K	Embossed tape (330mm)	10000
B	Packing in bulk	1000

L size	3.2 ± 0.15mm
W size	1.6 ± 0.15mm
T size	1.0 ± 0.1mm
Distance between external terminals P	0.8 ± 0.1mm
Size code in mm(inch)	3216 (1206)

Specifications

Capacitance	47000pF ± 20%
Rated voltage	16Vdc
Temperature characteristics (complied standard)	X7R(EIA)
Capacitance change rate	± 15.0%
Temperature range of temperature characteristics	-55 to 125
Operating temperature range	-55 to 125

⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.