



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: INTERNET350U

### Internet Office UPS System - Affordable full system protection for PCs and workstations



#### Highlights

- 350VA ultra-compact UPS
- Maintains 120V nominal output during blackouts
- Workstation optimized features include HID-compliant USB port, single line TEL / DSL line surge suppression and three surge-only outlets
- 99% line-mode efficiency saves energy and operating costs
- Input: NEMA 5-15P (120V 15A) / Output: 6 NEMA 5-15R (120V)
- 3 year product warranty / \$100,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

#### Description

Tripp Lite's INTERNET350U standby UPS system offers complete protection from blackouts, brownouts and transient surges on both AC and dialup modem lines. Provides seamless battery support during brownouts and power failures with enough runtime to save and shutdown connected equipment without data loss. Offers complete power protection in an ultra-compact, flat-pack housing with an appearance closer to a power strip than other bulky UPS designs. Includes 3 battery supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. USB port enables optional unattended system shutdown without data loss in the case of extended power failure. PowerAlert software available via free download from [www.tripplite.com](http://www.tripplite.com), includes bundled USB cable. Built-in single line RJ11 phone suppression jacks with line splitter protects up to two directly connected modems, fax machines, cordless phones or other peripherals with a standard dialup phone connection. Built-in audible alarm and front panel LEDs offer continuous status information regarding line and battery power operation. 350VA/180 watt power handling ability supports entry-level PC systems for up to 15 minutes during power fail conditions. 3 year warranty. \$100,000 [connected equipment insurance](#) (USA, Puerto Rico, & Canada Only).

#### Package Includes

- INTERNET350U UPS System
- USB communications cable
- Instruction manual with warranty information

#### Features

- INTERNET350U standby UPS offers complete protection from blackouts, brownouts and surges on both AC and TEL/DSL line connections
- 6 widely spaced outlets accommodate large transformer plugs without blocking outlets
- 3 battery supported outlets protect computer, monitor and vital system peripherals, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Provides battery derived AC output during blackouts and brownouts
- 350VA/180 watt power handling ability supports a variety of PCs, workstations and other sensitive electronics
- Supports entry-level PC systems up to 12 minutes during blackout conditions
- Built-in single line TEL/DSL line surge suppression protects modems, fax machines or cordless phones on a single phone line connection
- USB port, free PowerAlert software (available via web download) and cabling offer safe unattended shutdown without data loss during extended outages
- HID-compliant USB interface enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X.

- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment - ideal for unattended kiosk applications
- Space saving, ultra-compact housing fits almost anywhere

## Specifications

<b>OUTPUT</b>	
Output Volt Amp Capacity (VA)	350
Output Watt Capacity (watts)	180
Nominal Output Voltage(s) Supported	115v; 120v
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	6 5-15R outlet(s)
Surge suppression only outlets	3 UPS outlets, 3 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
<b>INPUT</b>	
Rated input current (at maximum load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P; Space saving right angled input plug
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
<b>BATTERY</b>	
Full load runtime (minutes)	3 minutes (180w)
Half load runtime (minutes)	11 minutes (90w)
DC system voltage	12V DC
Battery recharge rate (included batteries)	Less than 7 hours from 10% to 90%
<b>LEDS ALARMS &amp; SWITCHES</b>	

<b>LED Indicators</b>	2 LEDs indicate power status and overload/check battery status
<b>Alarms</b>	Audible alarm indicates power-failure and overload status
<b>Switches</b>	Combination switch controls on/off power status and self-test operation
<b>SURGE / NOISE SUPPRESSION</b>	
<b>UPS AC suppression joule rating</b>	380 joules
<b>UPS Dataline suppression</b>	1 line TEL / DSL protection (1 in / 1 out)
<b>EMI / RFI AC noise suppression</b>	Yes
<b>PHYSICAL</b>	
<b>Installation form factors supported with included accessories</b>	Tower; Ultra-compact desktop; Wallmount (using keyhole mounting tabs)
<b>Primary form factor</b>	Desktop
<b>UPS / Power Module dimensions in primary form factor (height x width x depth / inches)</b>	3 x 8 x 6.4
<b>UPS / Power Module dimensions in primary form factor (height x width x depth / cm)</b>	7.5 x 20.4 x 16.1
<b>Installed whole system dimensions in secondary form factor (height x width x depth / inches)</b>	
<b>UPS dimensions in secondary form factor (height x width x depth / cm)</b>	
<b>UPS / Power Module weight (lbs)</b>	5
<b>UPS / Power Module weight (kg)</b>	2.3
<b>Stepdown transformer dimensions (height x width x depth / inches)</b>	
<b>Stepdown transformer dimensions (height x width x depth / cm)</b>	
<b>Included battery pack dimensions (height x width x depth / inches)</b>	
<b>Included battery pack dimensions (height x width x depth / cm)</b>	
<b>UPS Shipping dimensions (height x width x depth / inches)</b>	4.1 x 11.3 x 7.7

<b>UPS Shipping dimensions (height x width x depth / cm)</b>	10.5 x 28.7 x 19.5
<b>Shipping weight (lbs)</b>	5.8
<b>Shipping weight (kg)</b>	2.6
<b>UPS housing material</b>	ABS
<b>ENVIRONMENTAL</b>	
<b>Operating Temperature Range</b>	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
<b>Storage Temperature Range</b>	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
<b>Relative Humidity</b>	0 to 95%, non-condensing
<b>AC mode BTU / hr. (full load)</b>	6.2
<b>Battery mode BTU / hr. (full load)</b>	134.3
<b>COMMUNICATIONS</b>	
<b>Communications interface</b>	USB (HID enabled)
<b>PowerAlert software</b>	Free download from <a href="http://www.tripplite.com">www.tripplite.com</a>
<b>Communications cable</b>	USB interface cable included
<b>WatchDog compatibility</b>	Supports Watchdog application, OS and hard-reboot restart options for remote applications
<b>LINE / BATTERY TRANSFER</b>	
<b>Transfer time</b>	2-4 milliseconds
<b>Low voltage transfer to battery power (setpoint)</b>	99
<b>High voltage transfer to battery power (setpoint)</b>	139
<b>SPECIAL FEATURES</b>	
<b>Cold Start (startup in battery mode during a power failure)</b>	Cold-start operation supported
<b>Green &amp; high efficiency features</b>	Greater than 95% efficiency - GREEN UPS
<b>CERTIFICATIONS</b>	
<b>UPS Certifications</b>	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); Meets FCC Part 68 / Industrie Canada (telecommunications); ROHS (Reduction of Hazardous Substances)
<b>WARRANTY</b>	
<b>Standard warranty period</b>	3 years
<b>Connected equipment insurance (USA, Canada, Puerto Rico)</b>	\$100,000 connected equipment insurance

---

## Related Items

### Optional Products

Product Type	Related Model	Description	Qty.
Audio Cables	<a href="#">CT120</a>	Instant-Read- AC Outlet Circuit Tester	-
Surge Protectors	<a href="#">DCATV</a>	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	-
Surge Protectors	<a href="#">DNET1</a>	Network Surge Suppressor - Essential protection for data and communication lines	-
Surge Protectors	<a href="#">DTEL2</a>	Network Surge Suppressor - Essential protection for data and communication lines	-
USB Cables & Adapters	<a href="#">U005-10I</a>	10-inch USB A/A Gold Extension Cable (USB-A Right Angle Male to USB-A Female)	-
USB Hubs/Accessories	<a href="#">U222-004-R</a>	4-Port USB2.0 Certified Ultra-Mini Hub	-
Software	<a href="#">WATCHDOGSW</a>	WatchDog Service Monitoring / Reboot Software	-
Extended Warranties	<a href="#">WEXT5-INTERNET</a>	5-Year Extended Warranty - For Internet Office Models	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2663](http://www.tripplite.com/en/products/model.cfm?txtModelID=2663).