



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: LC1800

Line Conditioner - Automatic voltage regulation with surge protection



Highlights

- Automatically adjusts low or high voltage
- 1800 watts
- 6 NEMA 5-15R outlets
- \$25,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

1800 watt (peak output) Automatic Voltage Regulation (AVR) system. Protects sensitive electronics, computer accessories and home theater equipment from power-related damage and performance problems. Extends the useful life of connected equipment by providing optimum voltage conditions for enhanced efficiency and cooler internal operating temperatures. Reliable transformer-based voltage correction circuits maintain 120V nominal output during voltage fluctuations between 89 and 147V. Three levels of voltage stabilization offer targeted response for overvoltages, undervoltages and severe brownouts. Prevents equipment damage and power related performance problems for computer accessories, printers, home theater equipment, a/v components and other sensitive electronic devices. Network-grade AC surge and EMI/RFI noise suppression. Supports loads up to 1800 watts (peak output) or 1500 watts (continuous output), 15A maximum. Includes 6 AC outlets, 6 ft AC line cord and 7 diagnostic LEDs which display incoming voltage level, surge suppression status and line fault status. 2 year warranty. \$25,000 [connected equipment insurance](#) (USA & Canada only).

Applications

- Maintains usable output voltage during severe brownouts and overvoltages for photocopiers, laser printers, fax machines, computers, audio/video equipment, CAD/CAM/CAE workstations, network nodes, file servers, phone systems, point-of-sale terminals, and other applications requiring steady input power.

Package Includes

- LC1800 Line Conditioner
- Mounting hardware
- Instruction manual

Features

- Maintains usable 120V nominal output during brownouts as low as 87V and overvoltages as high as 140V
- 1800 watts output power rating supports heavy 120V loads up to 15 amps
- Network grade surge suppression
- Complete EMI/RFI noise filtering
- 7 diagnostic LEDs indicate input voltage levels, surge suppression status and line fault conditions
- 6 protected NEMA5-15R outlets
- 6-ft. AC power cord with standard NEMA5-15P input plug
- 2 year manufacturers product warranty

- \$25,000 Ultimate Lifetime [connected equipment insurance](#) (USA & Canada Only)

Specifications

OUTPUT	
Output watts	1800
Output nominal voltage	120V / 60Hz
Outlet quantity / type	6 NEMA 5-15R6 NEMA5-15R
INPUT	
Input cord length (ft.)	6.00
Input cord length (m)	1.83
LEDS ALARMS & SWITCHES	
Front panel LEDs	7 LEDs show incoming voltage status, protection present and line fault conditions
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	1440 joules
EMI / RFI AC noise suppression	80 dB
PHYSICAL	
Shipping weight (lbs)	11.00
Shipping weight (kg)	4.99
Unit Dimensions (HWD/in)	6.75 x 5.75 x 6.75
Material of construction	Plastic
Form factors supported	Small Tower
WARRANTY	
Standard warranty period	2 years
Connected equipment insurance (USA, Canada, Puerto Rico)	\$25,000

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2833.