

Honeywell Sensing and Control

Search

LSE6C5

(Home : Products : Switches » MICRO SWITCH™ Limit Switches » MICRO SWITCH™ Heavy-Duty Limit Switches » HDLS)

narrow your search

- Products**
- Controls Monitoring and Lighting (286)
 - Machine Safety (1727)
 - Sensors (6158)
 - Switches (9781)
 - Wireless (45)

- Technology**
- Control and Instrumentation (890)
 - Electromechanical (9303)
 - Magnetic (538)
 - Platinum thin film (56)
 - Thick Film (1372)
 - More...



Actual product appearance may vary.

Series HDLS Plug In : Side Plunger - Standard; 2NC 2NO DPDT, Sequential; 0.5 in - 14NPT conduit

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) | [Specs](#) | [Documentation](#) | [Application Notes](#)

Product Specifications

Availability	Global
Operating Force (OF)	26,69 N max. [6 lb max.]
Pretravel (PT)	2,54 mm [0.10 in] max.
Overtravel (OT)	0.190 in min.
Differential Travel (DT)	0,89 mm [0.035 in] max.
Product Type	MICRO SWITCH™ Heavy-Duty Limit Switches
Actuator	Side Plunger - Standard
Circuitry	2NC 2NO DPDT Sequential, Snap Action, Double-Break
Ampere Rating	10 A (Thermal)
Supply Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Housing Type	HDLS Plug-in
Series Name	HDLS
Sealing	NEMA 1, 3, 4, 4X, 6, 6P, 12, 13
UL File #	E37138
Operating Temperature	-12 °C to 93 °C [10 °F to 200 °F]
Comment	Actuation: For in-line operation only; Side plunger to the back of switch
Agency Approvals and Standards	UL, CE, CSA, CCC, EN60947-1, EN60947-5-1
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial
Operating Position (OP)	33,0 mm [1.30 in]

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



[Wireless Web Site WGLA and WPMM XYR6000™](#)

[find out more](#)

white papers

- ▶ [Wireless Switches Offer Unlimited Benefit](#)
- ▶ [Basic Switches Are Not Created Equal](#)
- ▶ [Applying Precision Switches](#)
- ▶ [Sensors for Medical Devices](#)
- ▶ [New Ways to Measure Torque](#)
- ▶ [Choosing Safety Switches](#)
- ▶ [Specifying Hour Meters](#)

Need help?

[Click here to contact us](#)

contacts

- ▶ [Customer Service](#)
- ▶ [Technical Support](#)
- ▶ [Global Sales & Service](#)
- ▶ [View Site Demo](#)
- ▶ [Site Comments?](#)

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



▶ [Meet Dr. Larry](#)

my links

- ▶ [Login to iCOM](#)
- ▶ [Login to Rep/AD Portal](#)
- ▶ [Login to Digital University](#)

News Center

- ▶ [HONEYWELL INTRODUCES TRUSTABILITY® NSC SERIES, UNCOMPENSATED / UNAMPLIFIED BOARD MOUNT PRESSURE SENSORS](#)
- ▶ [HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER](#)
- ▶ [HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION](#)

