



Electronics

a vital part of your world

Find Answers:

Sunday, 16 October, 2005

CATALOG

- Cross Reference
  - Competitive Products
  - Military Spec P/Ns
  - Tyco Brand P/Ns

- Part Number Search
- Document Search
- Product Type Search
- Product Family Search
- Alphabetical Search
- RoHS/ELV Compliance & Alternates
- CAD Model Search
- Brand Search
- Tool Search
- Multiple Part Comparison
- Lead Free Solutions
- Help/Glossary

[Home](#)

e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

**Switches, Shunts, and Knobs**

**↳ Pushbutton Switches**

Alcoswitch **MPS203R** Active

Not ELV or RoHS Compliant

**(Corporate P/N: 7-1437567-2)**

Search for Compliant (RoHS/ELV)

Alternates

Search for Parts

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>General Info</li> <li>Sales Info</li> </ul>	<ul style="list-style-type: none"> <li>Pricing</li> <li>Product Availability</li> </ul>	<ul style="list-style-type: none"> <li>Tooling</li> </ul>

**Photos & Line Drawings** - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product View](#)

Searchable Features:	
Brand:	Alcoswitch
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Wave solder capable to 240°C
Product Type:	Switch
Tactile:	No
Configuration (Pole-Throw):	Double Pole - Double Throw
Contact Rating:	3A
Process Sealed:	No
Operating Function:	Momentary
Ganged:	No
Series:	MPS
Mount Style:	Panel

Other Properties:	
Contact Plating:	Silver
Case Material:	Epoxy resin
Actuator Material:	Nickel plated copper alloy
Spacer Height (mm [in]):	1.01 [0.040]
Temperature Rating:	Standard
Comment:	Order cap model C22 or C23.

<b>Mount Angle:</b>	Vertical
<b>Termination Type:</b>	Wire Lugs
<b>ESD Grounding Terminal:</b>	Without
<b>Low Profile:</b>	No
<b>Packaging Method:</b>	Loose Piece
<b>Actuator Style:</b>	Cap - Order Separately
<b>Actuator Length (mm [in]):</b>	8.00 [0.315]
<b>Actuator Profile:</b>	Extended
<b>Actuator Force (g [oz]):</b>	400.00 – 700.00 [14.000 – 25.000]
<b>Number of Actuators:</b>	Single
<b>Illuminated:</b>	No
<b>Dust Proof:</b>	No
<b>Support Bracket:</b>	Without
<b>Bushing Style:</b>	Threaded
<b>Bushing Diameter:</b>	1/4-40
<b>Snap Action:</b>	Yes

[Copyright and Privacy Statement](#)  
Visit [Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]

▪