



< List of part numbers with package codes >
NFM21PC105B1A3D

Shape

L size	2.0 ±0.2mm
W size	1.25 ±0.1mm
T size	0.85 ±0.1mm
External terminal width e	0.3±0.2mm
External terminal size i	0.6±0.2mm
External terminal size j	0.25±0.2mm
Distance between external terminals g	0.4±0.2mm
Size code in inch(mm)	0805 (2012M)

References


Packaging	Specifications	Minimum quantity
D	φ180mm Paper taping	4000
Mass (typ.)		
1 piece		12.0mg

Specifications

Capacitance	1.0μF ±20%
Rated voltage	10Vdc
Operating temperature range	-40 to 85°C
Rated Current	4A
DC Resistance(max.)	20mΩ

⚠ Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
 - 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.