






| REV. | DESCRIPTION | DATE |
|------|------------------------------|-----------|
| A | NEW DRAWING | 4/17/2006 |
| B | Changed pin thickness layout | 8/31/2006 |



TOLERANCE:
X.X ±0.2mm
X.XX ±0.1mm
X.XXX ±0.05mm



20050 SW 112th Ave.
Tualatin, OR 97062
Phone: 503-643-4899
800-275-4899
Fax: 503-372-1266
Website: www.cui.com

SPECIFICATIONS:
RATING: 24V DC @ 5A
CONTACT RESISTANCE: 50m OHMS MAX
INSULATION RESISTANCE: 50M OHMS MIN: 100V DC
VOLTAGE WITHSTAND: 500V AC R.M.S. FOR 1 MINUTE
LIFE: 5,000 CYCLES

| | |
|-----------|----------|
| MODEL NO. | PJ-002BH |
| SCHEMATIC | |

CENTER PIN DIAMETER 2.5mm

| | MATERIAL | PLATING |
|------------|--------------|---------|
| CENTER PIN | Copper | Nickel |
| TERMINAL 1 | Brass | Silver |
| TERMINAL 2 | Copper Alloy | Silver |
| TERMINAL 3 | Brass | Silver |
| HOUSING | PBT | |

| | | |
|----------------------|--------------|--------------------|
| TITLE: DC POWER JACK | | REV: B |
| PART NO. PJ-002BH | | UNITS: MM [INCHES] |
| DRAWN BY: ZRJ | APPROVED BY: | SCALE: 2:1 |

PC FILE NAME:
PJ-002BH

COPYRIGHT 2006 BY CUI INC.