

APC Replacement Battery Cartridge #12

Includes: All required connectors, Authorized Return Service (ARS) tag (currently available in the US only), Battery recycling guide, Installation Guide, Reusable packaging

Part Number : **RBC12**

- [Email Technical Specifications](#)
- [Printer Friendly](#)

- Additional Information**
- [User Manual & Installation Guides](#)
 - [Product Distribution](#)



[+] More Images

Technical Specifications

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	Stand alone battery stack
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1
Replacement battery cartridge note	RBC 12 is composed of two seperate battery cells. The Net dimensions are measured per cell.

Features:

- o Hot Swap Batteries
- o Plug-and-Play installation

Physical

Net Weight	44.00 lbs. (20.00 kg)
Maximum Height	3.80 inches (97 mm)
Maximum Width	10.00 inches (254 mm)
Maximum depth	6.00 inches (152 mm)
Shipping Weight	50.30 lbs. (22.86 kg)
Shipping Width	15.50 inches (394 mm)
Shipping Height	9.00 inches (229 mm)
Shipping Depth	22.50 inches (572 mm)
Color	Black
Units per Pallet	20.00

Environmental

Operating Environment	0 - 40 °C (32 - 104 °F)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-15 - 45 °C (5 - 113 °F)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Standard Warranty	1 year repair or replace
-------------------	--------------------------