



RBC24

APC Replacement Battery Cartridge #24

Part Number: RBC24

Batteries & Runtime

Battery Volt-Amp-Hour Capacity	432
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	Enclosed battery cartridge
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1

Physical

Net Weight	26.31 lbs. (11.96 kg)
Maximum Height	3.25 inches (83 mm)
Maximum Width	8.50 inches (216 mm)
Maximum depth	13.50 inches (343 mm)
Shipping Weight	27.72 lbs. (12.60 kg)
Shipping Width	14.50 inches (368 mm)
Shipping Height	6.00 inches (152 mm)
Shipping Depth	19.50 inches (495 mm)
Color	Black
Units per Pallet	18.00

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Standard Warranty	1 year repair or replace
-------------------	--------------------------

*Estimated Resale Price - Without Tax/VAT