

## APC Replacement Battery Cartridge #5

Includes: All required connectors, Authorized Return Service (ARS) tag (currently available in the US only), Battery recycling guide, Installation Guide, Reusable packaging

Part Number : **RBC5**

- [Email Technical Specifications](#)
- [Printer Friendly](#)

### Additional Information

- [User Manual & Installation Guides](#)
- [Product Distribution](#)



[+] More Images

## Technical Specifications

### Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	--
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1

### Features:

- o Hot Swap Batteries
- o Plug-and-Play installation

### Physical

Net Weight	10.90 lbs. ( 4.95 kg)
Maximum Height	3.70 inches ( 94 mm)
Maximum Width	5.10 inches (130 mm)
Maximum depth	5.90 inches (150 mm)
Shipping Weight	12.00 lbs. ( 5.45 kg)
Shipping Width	6.60 inches (168 mm)
Shipping Height	6.60 inches (168 mm)
Shipping Depth	8.80 inches (224 mm)
Color	Black
Units per Pallet	100.00

### Environmental

Operating Environment	0 - 40 °C (32 - 104 °F)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-15 - 45 °C (5 - 113 °F)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)

### Conformance

Standard Warranty	1 year repair or replace
-------------------	--------------------------