



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: RS-1215-RA

**Power Strip - Multiple outlets wherever you need them**

### Highlights

- Outlets placed at **right angle** to accommodate bulky transformers
- 12 widely spaced outlets (6 front / 6 rear)
- Designed for standard 19-in. racks (1U high)
- 15-ft. cord
- 15A circuit breaker



### Description

Tripp Lite's RS-1215-RA Power Strip offers 15A capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19-in. rack meeting EIA standards. Unfiltered electrical pass-through makes RS-1215-RA ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Features 12 NEMA5-15R outlets (6 front/6 rear) placed at a right angle (with ground pin at bottom), 15-ft. AC power cord and lighted power switch with cover that prevents risk of accidental turn-off.

PLUG/OUTLETS: Input: NEMA 5-15P

Output: 12 x NEMA 5-15R (6 front/6 rear)

ELECTRICAL: 120V AC, 50/60Hz, 20A (Requires NEMA 5-15R wall receptacle)

FORMAT: 19-in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

#### Applications

- Offers multiple outlet power distribution for multiple loads in 19-in. rackmount, wallmount and under-counter applications such as internetworking, PC systems, telecommunications, audio/video, security, sound reinforcement and more. Ideal for distribution of UPS-, generator- or commercially derived AC power to protected equipment.

#### Package Includes

- RS-1215-RA 1U Rackmount Power Strip
- Instruction manual with warranty information

### Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19-in. rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 12 x NEMA5-15R output receptacles (6 front/6 rear)
- 15-ft. AC cord with NEMA5-15P plug

- Right-angle outlet orientation with ground pin at the bottom
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 15A electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

## Specifications

SYSTEM OVERVIEW	
Voltage compatibility	120VAC
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output volt amp capacity (amps)	15A
Outlet quantity / type	12 NEMA 5-15R
Outlet orientation	6 front-facing / 6 rear-facing, all with ground pin oriented to the bottom (when viewed in 1U rackmount configuration)
INPUT	
Recommended Electrical Service	15A 120V
Input connection type	NEMA 5-15P
Input cord length (ft.)	15
Input cord length (m)	4.572
LEDS ALARMS & SWITCHES	
Switches	Red illuminated - position switch controls power to all outlets
Locking switch cover	Transparent locking switch cover prevents accidental shutoff
PHYSICAL	
Unit Dimensions (HWD/in)	1.75 (1U) x 17.5 x 4.5
Unit Dimensions (HWD/cm)	4.445 x 44.45 x 11.4
Material of construction	Sheet metal
Receptacle Color	Black
AC line cord color	Black
Form factors supported	1U rackmount, wall-mount and undercounter installation supported
SPECIAL FEATURES	
TVSS grounding	Back panel nut-and-bolt grounding lug
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363 (UR status)
cUL / CSA (Canada)	cUL
WARRANTY	
Standard warranty period	Lifetime

---

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=203](http://www.tripplite.com/en/products/model.cfm?txtModelID=203).

---

© 2010 Tripp Lite. All Rights Reserved.