


SLW-120-01-T-S

CES-115-01-T-S



SLW-110-01-T-D

CES-125-01-T-D

SLW, CES SERIES

(2,54 mm) .100"

LOW PROFILE SOCKET STRIPS

SPECIFICATIONS

For complete specifications see www.samtec.com?SLW or www.samtec.com?CES

Insulator Material:

Black G.F. Polyester

Contact Material:

Phosphor Bronze

Plating: Au or Sn over 50µ" (1,27 µm) Ni

SLW Current Rating (SLW/TSW):

5,2 A per pin (1 pin powered per row)

CES Current Rating (TSW/CES):

5,5 A per pin (1 pin powered per row)

Voltage Rating:

SLW: 50 VAC

CES: 400 VAC

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:

10 mΩ

Insertion Depth:

SLW: (2,16 mm) .085" to (2,92 mm) .115"

CES: (2,62 mm) .103" to (4,06 mm) .160"

Insertion Force:

SLW: (Single contact only) (3,34 N) 12 oz avg.

(0,64 mm) .025" SQ pin

CES: (Single contact only) (2,22 N) 8 oz avg.

(0,64 mm) .025" SQ pin

Withdrawal Force:

SLW: (Single contact only) (1,67 N) 6 oz avg.

(0,64 mm) .025" SQ pin

CES: (Single contact only) (1,11 N) 4 oz avg.

(0,64 mm) .025" SQ pin

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.

SLW	1	NO. PINS PER ROW	01	PLATING OPTION	ROW OPTION
01 thru 50					
TIGER BUY CONTACT					
<p>-S = Single Row</p> <p>-D = Double Row</p> <p>-F = Gold flash on contact, Matte Tin on tail</p> <p>-L = 10µ" (0,25 µm) Gold on contact, Matte Tin on tail</p> <p>-G = 20µ" (0,51 µm) Gold on contact, Gold flash on balance</p> <p>-T = Matte Tin</p>					
<p>Mates with: TLW, TSW, MTLW, MTSW, HW, EW, ZW, HTSW, HMTSW, TSM</p>					

CES	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	RA OPTION
01 thru 50						
<p>-01 = (3,25 mm) .128 "A" Dim.</p> <p>-02 = (5,66 mm) .223 "A" Dim.</p> <p>-L = 10µ" (0,25 µm) Gold contact, Matte Tin on tail</p> <p>-T = Matte Tin</p> <p>-S = Single Row</p> <p>-D = Double Row</p> <p>-RA = Right Angle version</p> <p>Style -02 only Single Row only</p>						
<p>Mates with: TLW, TSW, MTLW, MTSW, HW, EW, ZW, DW, HTSW, PHT, HMTSW</p>						

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM