

SLW, CES SERIES

(2,54 mm) .100"

LOW PROFILE SOCKET STRIPS

SPECIFICATIONS

For complete specifications see www.samtec.com?SLW or www.samtec.com?CES

Insulator Material:

Black G.F. Polyester

Contact Material:

Phosphor Bronze

Plating: Au or Sn over

50µ" (1,27 µm) Ni

SLW Current Rating (SLW/TSW):

5.2 A per pin

(1 pin powered per row)

CES Current Rating (TSW/CES):

5.5 A per pin

(1 pin powered per row)

Voltage Rating:

SLW: 406 VAC

CES: 400 VAC

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:

10 mΩ

Insertion Depth:

SLW: (2,16 mm) .085" to

(2,92 mm) .115"

CES: (2,62 mm) .103" to

(4,06 mm) .160"

Insertion Force:

SLW: (Single contact only)

(3,34 N) 12 oz avg.

(0,64 mm) .025" SQ pin

CES: (Single contact only)

(2,22 N) 8 oz avg.

(0,64 mm) .025" SQ pin

Withdrawal Force:

SLW: (Single contact only)

(1,67 N) 6 oz avg.

(0,64 mm) .025" SQ pin

CES: (Single contact only)

(1,11 N) 4 oz avg.

(0,64 mm) .025" SQ pin

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.

SLW	1	NO. PINS PER ROW	01	PLATING OPTION	ROW OPTION
------------	----------	-------------------------	-----------	-----------------------	-------------------

Mates with:
TLW, TSW, MTLW, MTSW, HW, EW, ZW, HTSW, HMTSW, TSM




- F** = Gold flash on contact, Matte Tin on tail
- L** = 10µ" (0,25 µm) Gold on contact, Matte Tin on tail
- G** = 20µ" (0,51 µm) Gold on contact, Gold flash on balance
- T** = Matte Tin

- S** = Single Row
- D** = Double Row

CES	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	RA OPTION
------------	----------	-------------------------	-------------------	-----------------------	-------------------	------------------

Mates with:
TLW, TSW, MTLW, MTSW, HW, EW, ZW, DW, HTSW, PHT, HMTSW



- 01** = (3,25 mm) .128 "A" Dim.
- 02** = (5,66 mm) .223 "A" Dim.
- L** = 10µ" (0,25 µm) Gold contact, Matte Tin on tail
- T** = Matte Tin

- S** = Single Row
 - D** = Double Row
 - RA** = Right Angle version
 - Style -02 only Single Row only
-

