

**NEW
PRODUCT**




SPECIFICATIONS

Contact Rating:	12VDC, 50mA
Life Expectancy:	50,000 cycles minimum
Contact Resistance:	100mΩ max., 100MΩ min.
Insulation Resistance:	10000 MΩ min.
Dielectric Strength:	250 VAC
Actuator Force:	160 ± 50 gf min.
Operating Temperature:	-20°C to +70°C
Storage Temperature:	-40°C to +80°C

MATERIALS

Housing:	Nylon 46
Actuator:	Nylon 46
Cover:	Stainless Steel
Contacts:	Stainless Steel
Terminals:	Brass
Travel:	0.20 +/-0.10mm
Tape & Reel:	2500 pieces per reel

HOW TO ORDER



ACTUATOR LENGTH

TL 1014 Boss
A= no boss
A= boss

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.