



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TLP810NET

### Protect It! Surge Suppressor



### Highlights

- 8 outlets / 10-ft. cord
- 3690 joule rating
- Coaxial surge protection (digital broadband quality accommodates 2.2GHz bandwidth)
- Ethernet surge protection
- 2-line modem/fax surge protection
- \$250,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

### Description

Tripp Lite's TLP810NET surge suppressor has 8 outlets, a 10-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 3690 joules to handle the strongest surges. Built-in RJ11, RJ45, and Type F coax jacks prevent surges from damaging your modem/fax/10BT/cable/satellite equipment. Coaxial jacks provide digital broadband quality and can handle 2.2GHz bandwidth. \$250,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

### Applications

- Personal computers, modems, CAD/CAM/CAE workstations, network nodes, file servers, point-of-sale terminals, audio/visual devices, and more.

### Package Includes

- TLP810NET
- 6-ft. telephone cord
- 6-ft. network cable
- 6-ft. coax cable
- Instruction manual with warranty information

### Features

- 8 outlets with integrated child safety covers; black housing
- 10-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment on 2 lines simultaneously; 6-ft. telephone cord included
- Built-in RJ45 jacks prevent surges from damaging your 10BT equipment; 6-ft. network cable included
- Built-in gold, Type F coax jacks prevent surges from damaging your cable/satellite equipment; digital broadband quality accommodates 2.2GHz bandwidth; 6-ft. coax cable included
- Surge suppression rating: 3690 joules
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- \$250,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)
- Diagnostic LEDs indicate protection present & ground present
- Audible alarm notifies user when the unit is damaged and needs to be replaced

- Keyhole supports for wall mounting
- Lighted power switch
- Lifetime product warranty

## Specifications

OVERVIEW	
Intended Application	Home/Office, Computer Networks
SYSTEM OVERVIEW	
Voltage compatibility	120 VAC
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Output volt amp capacity (amps)	15
Outlet quantity / type	8 NEMA 5-15R
Transformer accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 6 transformers total
Outlet safety covers	Includes built-in sliding outlet safety covers
Outlet orientation	Single row of 5, plus a second row of 3 for transformer accommodation
INPUT	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right-angle input plug
Input cord length (ft.)	10 ft.
Input cord length (m)	3.0
Input cord gauge, type	14 gauge, SJT
LEDS ALARMS & SWITCHES	
Alarms	Audible alarm sounds to indicate damage to suppression components
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	3690 joules
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150V
UL1499 let through rating	330V - UL Verified
EMI / RFI filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	

Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	2 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line (supports 2.2 GHz bandwidths)
Network (Ethernet) Protection	Yes
<b>PHYSICAL</b>	
Shipping weight (lbs)	2.8
Shipping weight (kg)	1.3
Unit Dimensions (HWD/in)	1.6 x 9.25 x 4.25
Unit Dimensions (HWD/cm)	4.1 x 23.5 x 10.8
Shipping Dimensions (HWD/in)	2.5 x 14.75 x 8.75
Shipping Dimensions (HWD/cm)	6.4 x 37.5 x 22.2
Unit weight (lbs)	2
Unit weight (kg)	0.9
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
AC line cord color	Black
Style	Strip
<b>SPECIAL FEATURES</b>	
Right-Angle Plug	Yes
<b>CERTIFICATIONS</b>	
UL1449 1998 Rev. (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Standard warranty period	Lifetime

<b>Connected equipment insurance (USA, Canada, Puerto Rico)</b>	\$250,000
---	-----------

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=144](http://www.tripplite.com/en/products/model.cfm?txtModelID=144).

---

© 2010 Tripp Lite. All Rights Reserved.