


**KEMET Part Number: TRS1-0MLR00V**  
(USEC00MLR00000)

KEMET, TRS, Thermal Reed Switch, Axial, 2.5C Temperature Accuracy, High Reliability, High-Speed Response, Long Operational Life, Excellent Environmental Durability, High Temperature Accuracy, 0°C, Make



General Information	
<b>Series:</b>	TRS
<b>Type:</b>	Thermal Reed Switch
<b>Style:</b>	Axial
<b>Description:</b>	Thermal Reed Switch
<b>Features:</b>	High Reliability, High-Speed Response, Long Operational Life, Excellent Environmental Durability, High Temperature Accuracy
<b>Lead:</b>	Cables
<b>RoHS:</b>	Yes

Dimensions	
<b>D</b>	7.65mm
<b>L</b>	54mm
<b>L2</b>	34mm
<b>T</b>	18.8mm
<b>LL</b>	200mm

Packaging Specifications	
<b>Packaging:</b>	Rubberband Box
<b>Packaging Quantity:</b>	500
<b>Weight:</b>	8.5 g

Specifications	
<b>Switching Temperature:</b>	0C +/-2.5C
<b>Temperature Range:</b>	-20/+130C
<b>Contact Type:</b>	Make
<b>Voltage DC:</b>	1500 VAC/1 minute or 1800 VAC/1 second
<b>Voltage AC:</b>	220 VAC MAX (Opening/Closing)
<b>Current:</b>	0.045 Amps AC MAX (Opening/Closing), 1 mAmps MIN (5VDC, Opening/Closing)
<b>Resistance:</b>	150 mOhms MAX (Contact Resistance)
<b>Max Opening/Closing Power:</b>	10 W (AC)
<b>Max Opening/Closing Voltage:</b>	220 V (AC)
<b>Differential Temperature:</b>	10C Maximum