



Electronics

a vital part of your world

Find Answers:

Sunday, 23 October, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Modular Plugs and Jacks

↳ PCB Mounted Jacks - Single Port, Multi-port and Stacked

AMP 520250-2 [Active](#)

[Not ELV or RoHS Compliant](#)

(Corporate P/N: 520250-2)

[Search for Compliant \(RoHS/ELV\)](#)

[Alternates](#)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> General Info Sales Info Assembly Subcontractors 	<ul style="list-style-type: none"> Pricing & Availability 	<ul style="list-style-type: none"> Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Wave solder capable to 240°C
Product Type:	Jack
Port Configuration:	Single
Jack Configuration:	1 x 1
Jack Type:	RJ14
Number of Positions:	6
PCB Mount Angle:	Side Entry (Right Angle)
PCB Mount Style:	Thru Hole
PCB Termination Type:	Solder

Other Properties:	
Housing Material:	Polyester (PBT)
Housing Material Flammability Rating:	UL 94V-0
Flanged:	No
Contact Material:	Phosphor Bronze
Latch Style:	Standard
PCB Thickness (mm [in]):	1.57 [0.062]
Packaging Method:	Tray

<u>Shielded:</u>	No
<u>Performance Category:</u>	Cat 3
<u>Height (mm [in]):</u>	16.20 [0.638]
<u>Inverted Jack Face:</u>	No
<u>LED:</u>	Without
Number of Contacts Loaded:	4
<u>Grounding Options:</u>	Without
<u>PCB Tail Length (mm [in]):</u>	3.81 [0.150]
<u>Solder Tail Plating:</u>	Tin-Lead over Nickel
<u>Panel Stops:</u>	With
<u>Contact Mating Area Plating:</u>	Gold (50) over Nickel (50)
<u>Keyed:</u>	No
<u>Profile:</u>	Standard
<u>Panel Attachment:</u>	Yes
IR Reflow Compatible:	No
<u>Color:</u>	Black

Copyright and [Privacy Statement](#)
 Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]