

543945 Coax - Surveillance and CCTV Applications

		<p>For more information please call 1-800-Belden1</p> <p><u>See Put-ups and Colors</u></p>
---	--	---

Description:

20 AWG solid bare copper conductor, foam polyethylene insulation, bare copper braid shield, PVC jacket, sequential footage marking every two feet.

SUITABLE APPLICATIONS:

Suitable Applications	Analog Video/CCTV Coax.
-----------------------	-------------------------

PHYSICAL CHARACTERISTICS:

CONDUCTOR:

Number of Coax	1
RG Type	59/U
Series Type	Series 59
AWG	20
Stranding	Solid
Conductor Diameter	.032 in.
Conductor Material	BC - Bare Copper

INSULATION:

Insulation Material	Gas-injected FPE - Foam Polyethylene
Insulation Diameter	.145 in.

OUTER SHIELD:

Outer Shield Type	Braid
Outer Shield Material	BC - Bare Copper
Outer Shield % Coverage	95 %

OUTER JACKET:

Outer Jacket Material	PVC - Polyvinyl Chloride
-----------------------	--------------------------

OVERALL NOMINAL DIAMETER:

Overall Nominal Diameter	.232 in.
--------------------------	----------

MECHANICAL CHARACTERISTICS:

Operating Temperature Range	-30°C To +75°C
UL Temperature Rating	75°C
Bulk Cable Weight	29 lbs/1000 ft.
Max. Recommended Pulling Tension	57 lbs.

543945 Coax - Surveillance and CCTV Applications

Min. Bend Radius (Install)	2.5 in.
----------------------------	---------

APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

APPLICABLE STANDARDS:

NEC/(UL) Specification	CM
NEC Articles	800
CEC/C(UL) Specification	CM
EU CE Mark (Y/N)	Yes
EU RoHS Compliant (Y/N)	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004

FLAME TEST:

UL Flame Test	UL1685 UL Loading
C(UL) Flame Test	FT1

SUITABILITY:

Suitability - Indoor	Yes
Suitability - Outdoor	Yes - Black only
Suitability - Aerial	Yes - Black only

PLENUM/NON-PLENUM:

Plenum (Y/N)	N
--------------	---

ELECTRICAL CHARACTERISTICS:

Nom. Characteristic Impedance	75 Ohms
Nom. Inductance	.097 μ H/ft
Nom. Capacitance Conductor to Shield	16.3 pF/ft
Nominal Velocity of Propagation	83 %
Nominal Delay	1.21 ns/ft
Nom. Conductor DC Resistance @ 20 Deg. C	10.0 Ohms/1000 ft
Nominal Outer Shield DC Resistance @ 20°C	3.5 Ohms/1000 ft

Nom. Attenuation :

Description	Frequency (MHz)	Start Frequency (MHz)	Stop Frequency (MHz)	Nom. Attenuation (dB/100 ft.)
	1			.30
	5			.65
	10			.90
	50			1.90
	100			2.60
	200			3.60
	400			5.00
	700			7.00
	900			8.00
	1000			8.50

543945 Coax - Surveillance and CCTV Applications

PUT-UPS AND COLORS:

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
543945 0091000	RG-59/U COAX	1000	31	WHITE	C
543945 009500	RG-59/U COAX	500	16	WHITE	
543945 009U1000	RG-59/U COAX	U1000	25	WHITE	
543945 009U500	RG-59/U COAX	U500	12.5	WHITE	
543945 0101000	RG-59/U COAX	1000	24	BLACK	C
543945 010500	RG-59/U COAX	500	13	BLACK	C
543945 010U1000	RG-59/U COAX	U1000	25	BLACK	
543945 010U500	RG-59/U COAX	U500	12.5	BLACK	

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 09-29-2005

© Copyright 2006 Belden, Inc
All Rights Reserved.

Although Belden ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with the following environmental regulations: California Proposition 65 Consent Judgment For Wire & Cable Mfgs.(San Francisco Superior Court Nos. 312962 And 320342); EU RoHS (Directive 2002/95/EC, 27-Jan-2003);Material manufactured prior to the compliance date may still be in stock at Belden facilities and in our Distributor's inventory. EU ELV (Directive 2000/53/EC, 18-Sept-2000); EU WEEE (Directive 2002/96/EC, 27-Jan-2003); And EU BFR (Directive 2003/11/EC, 6-Feb-2003). The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information and belief at the date of its publication. The information provided in the Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.