



Electronics

a vital part of your world

Find Answers:

Friday, 18 November, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

Circuit Breakers

↳ Magnetic Circuit Breakers M9/W9 - Standard Size



W92-X112-15 Active

[Not ELV or RoHS Compliant](#)

(Corporate P/N: 7-1393254-0)

[Search for Compliant \(RoHS/ELV\)](#)

[Alternates](#)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>➤ <a href="#">General Info</a></li> <li>➤ <a href="#">Sales Info</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Pricing &amp; Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Tooling</a></li> </ul>

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

- [Product Photo](#)
- [Schematic](#)
- [Panel Cutout](#)
- [Front View](#)

Searchable Features:

<b>Brand:</b>	Potter & Brumfield
<b>RoHS/ELV Compliance:</b>	Not ELV/RoHS compliant
<b>Lead Free Solder Processes:</b>	Not relevant for lead free process
<b>Series/Mounting Option:</b>	W9 (6-32 Mtg. Threads)
<b>Actuator Style:</b>	Toggle
<b>Number of Poles:</b>	2
<b>Current Rating (Amps.):</b>	15
<b>Toggle Color:</b>	Black
<b>Circuit Function:</b>	Series Trip
<b>Operating Voltage, Max.:</b>	277 VAC
<b>Trip Time at 200%:</b>	2.2 to 20 Seconds

Other Properties:

<b>Approved Standards:</b>	UL Recognized, CSA Certified
----------------------------	------------------------------

<b><a href="#">Interrupt Capacity:</a></b>	5,000 A @ 277 VAC
<b><a href="#">Termination Type:</a></b>	10-32 Stud

[Copyright and Privacy Statement](#)  
Visit [Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]