



Designers' Choice

NEW PRODUCT BULLETIN

New COLOR CODED SCREW TERMINALS



Color Coded Screw Terminals provide:

- Quick identification
- Visibility for field service troubleshooting

SPECIFICATIONS

Combination Binding Head:

Standard screw is Brass, Nickel Plate. For painted, color head, add suffix as shown.



6-32 x 1/4 L. THREAD

COLOR SELECTION:

Select desired screw terminal and add color suffix to the screw terminal Cat. No.

HEAD COLOR	SUFFIX
RED	-2
BLACK	-3
WHITE	-4
BLUE	-5
GREEN	-6
YELLOW	-7
NICKEL	none

CAT. NO. COLOR SUFFIX
Ex: XXXX -X



• Available for screw terminals where noted.

LOW PROFILE - PC SCREW TERMINALS

These easy to mount screw terminals are ideally suited for high density packaging and are available unassembled or with the screw installed and captivated. They are a practical alternative to PC screw type edge connectors, barrier blocks, terminal boards and terminal strips.

PRINCIPAL FEATURES

- Low profile
- Stable, no-rock design
- Easily mounts in pre-drilled or stamped holes
- Accepts 12-22 AWG solid or stranded wire, crimp type terminals or lugs
- Space saving and time saving
- Combination drive, binding head screw

New Color coded screws available (add color screw suffix to Cat. No.)



SPECIFICATIONS

Rated: 15 Amps

Terminal:

.032 Brass, Tin Plate


Binding Head Screw:

Brass, Nickel Plate


CAT. NO. 7784
(Supplied Less Screw)

CAT. NO. 8198
(Screw Supplied Unassembled)

CAT. NO. 7778
(Screw Installed & Captivated)



Mounting Detail



A practical, low-cost alternative to PC screw type edge connectors, barrier blocks, terminal boards and terminal strips. Supplied unassembled or with screw installed and captivated.

PRINCIPAL FEATURES

- Low profile
- Stable, no-rock design with exclusive anti-rotational feature
- Ideally suited for high-density packaging
- Space saving and time saving
- Combination drive, binding head screw

New Color coded screws available (add color screw suffix to Cat. No.)



SPECIFICATIONS

Rated: 15 Amps

Terminal:

.032 Brass, Tin Plate


Binding Head Screw:

Brass, Nickel Plate


CAT. NO. 7785
(Supplied Less Screw)

CAT. NO. 8195
(Screw Supplied Unassembled)

CAT. NO. 7775
(Screw Installed & Captivated)



Mounting Detail



30 AMP - PC SCREW TERMINALS

A practical, low-cost alternative to PC screw type edge connectors, barrier blocks, terminal boards and terminal strips. Supplied unassembled or with screw installed and captivated.

PRINCIPAL FEATURES

- Compact, heavy duty design
- Six snap-in legs for total stability
- Serrated top surface secures connection
- Combination drive, binding head screw

New Color coded screws available (add color screw suffix to Cat. No.)



SPECIFICATIONS

Rated: 30 Amps

Terminal:

.032 Brass, Tin Plate


Binding Head Screw:

Brass, Nickel Plate


CAT. NO. 7786
(Supplied Less Screw)

CAT. NO. 8197
(Screw Supplied Unassembled)

CAT. NO. 8199
(Screw Installed & Captivated)



Mounting Detail



HEAVY DUTY

This heavy duty screw terminal has been designed to carry 30 Amps, while maintaining a space saving compact profile, making it ideal for high density packaging.

PRINCIPAL FEATURES

- Compact, heavy duty design
- Six snap-in legs for total stability
- Serrated top surface secures connection



SPECIFICATIONS

Rated: 30 Amps


Terminal:

.045 Brass, Tin Plate


Screw: Stainless Steel

CAT. NO. 7787
(Supplied Less Screw)

CAT. NO. 8196
(Screw Supplied Unassembled)



Mounting Detail





PC MOUNT SCREW TERMINALS

These easy-to-mount, multipurpose screw type terminals are a practical, low-cost alternative to PC screw type edge connectors, barrier blocks, terminal boards and terminal strips. Steadfast and easy to install, will accommodate solid or stranded wire, crimp type terminals or lugs. Multi-placement of these low-profile terminals make them ideally suited for high density packaging. Supplied unassembled or with screw installed and captivated.

PRINCIPAL FEATURES

- Low profile
- Stable, no-rock design with exclusive anti-rotational feature
- Easily mounts with four legs into pre-drilled or punched holes
- Accepts 14-22 AWG solid or stranded wire, crimp type terminals or lugs
- Ideally suited for high-density packaging
- Available in horizontal or vertical mounting
- Space-saving and time saving
- Easy accessibility for PC board testing
- Binding screw is positioned above board level to avoid wicking during wave soldering
- Terminals are made of Brass with Tin Plate
- Supplied with a combination drive 6-32 binding head screw

New Color coded screws available (add color screw suffix to Cat. No.)




CAT. NO. 7779 (Supplied Less Screw)
CAT. NO. 7690 (Screw Supplied Unassembled)
CAT. NO. 7692 (Screw Installed & Captivated)


HORIZONTAL TYPE

SPECIFICATIONS
Rated: 15 Amps
Terminal: .032 Thick Brass, Tin Plate
Binding Head Screw: Brass, Nickel Plate

New Color coded screws available (add color screw suffix to Cat. No.)



CAT. NO. 7781 (Supplied Less Screw)
CAT. NO. 8190 (Screw Supplied Unassembled)
CAT. NO. 7700 (Screw Installed & Captivated)




CAT. NO. 7780 (Supplied Less Screw)
CAT. NO. 7691 (Screw Supplied Unassembled)
CAT. NO. 7693 (Screw Installed & Captivated)

VERTICAL TYPE


SPECIFICATIONS
Rated: 15 Amps
Terminal: .032 Thick Brass, Tin Plate
Binding Head Screw: Brass, Nickel Plate

New Color coded screws available (add color screw suffix to Cat. No.)



CAT. NO. 7782 (Supplied Less Screw)
CAT. NO. 8191 (Screw Supplied Unassembled)
CAT. NO. 7701 (Screw Installed & Captivated)

EXTENDED





CAT. NO. 7789 (Supplied Less Screw)
CAT. NO. 7697 (Screw Supplied Unassembled)
CAT. NO. 7699 (Screw Installed & Captivated)

SPECIFICATIONS

Rated: 15 Amps
Terminal: .032 Thick Brass, Tin Plate
Binding Head Screw: Brass, Nickel Plate

New Color coded screws available (add color screw suffix to Cat. No.)

45°



CAT. NO. 7783 (Supplied Less Screw)
CAT. NO. 8189 (Screw Supplied Unassembled)
CAT. NO. 7702 (Screw Installed & Captivated)



Designers' Choice

PC SCREW TERMINALS

LOW PROFILE - PC SCREW TERMINALS

These easy to mount screw terminals are ideally suited for high density packaging and are available unassembled or with the screw installed and captivated. They are a practical alternative to PC screw type edge connectors, barrier blocks, terminal boards and terminal strips.


PRINCIPAL FEATURES

- Low profile
- Stable, no-rock design
- Easily mounts in pre-drilled or stamped holes
- Accepts 12-22 AWG solid or stranded wire, scrimp type terminals or lugs
- Space saving and time saving
- Combination drive, binding head screw




SPECIFICATIONS

Rated: 15 Amps
Terminal:
.032 Brass, Tin Plate
Binding Head Screw:
Brass, Nickel Plate



Mounting Detail



CAT. NO. 7784
(Supplied Less Screw)

CAT. NO. 8198
(Screw Supplied Unassembled)

CAT. NO. 7778
(Screw Installed & Captivated)

A practical, low-cost alternative to PC screw type edge connectors, barrier blocks, terminal boards and terminal strips. Supplied unassembled or with screw installed and captivated.


PRINCIPAL FEATURES

- Low profile
- Stable, no-rock design with exclusive anti-rotational feature
- Ideally suited for high-density packaging
- Space saving and time saving
- Combination drive, binding head screw




SPECIFICATIONS

Rated: 15 Amps
Terminal:
.032 Brass, Tin Plate
Binding Head Screw:
Brass, Nickel Plate



Mounting Detail



CAT. NO. 7785
(Supplied Less Screw)

CAT. NO. 8195
(Screw Supplied Unassembled)

CAT. NO. 7775
(Screw Installed & Captivated)

30 AMP - PC SCREW TERMINALS

A practical, low-cost alternative to PC screw type edge connectors, barrier blocks, terminal boards and terminal strips. Supplied unassembled or with screw installed and captivated.


PRINCIPAL FEATURES

- Compact, heavy duty design
- Six snap-in legs for total stability
- Serrated top surface secures connection
- Combination drive, binding head screw




SPECIFICATIONS

Rated: 30 Amps
Terminal:
.032 Brass, Tin Plate
Binding Head Screw:
Brass, Nickel Plate



Mounting Detail



CAT. NO. 7786
(Supplied Less Screw)

CAT. NO. 8197
(Screw Supplied Unassembled)

CAT. NO. 8199
(Screw Installed & Captivated)

HEAVY DUTY

This heavy duty screw terminal has been designed to carry 30 Amps, while maintaining a space saving compact profile, making it ideal for high density packaging.


PRINCIPAL FEATURES

- Compact, heavy duty design
- Six snap-in legs for total stability
- Serrated top surface secures connection




SPECIFICATIONS

Rated: 30 Amps
Terminal:
.045 Brass, Tin Plate
Screw: Stainless Steel



Mounting Detail



CAT. NO. 7787
(Supplied Less Screw)

CAT. NO. 8196
(Screw Supplied Unassembled)

CUSTOM PC SCREW TERMINALS

Keystone is fully integrated to meet your total design & production needs.

Manufacturing custom designs & modifications of standard items is our specialty.

Quotations on special PC screw terminals furnished promptly upon receipt of sample, sketch, print or CAD drawings.

PC SCREW TERMINALS

Designers' Choice





PC MOUNT SCREW TERMINALS

These easy-to-mount, multipurpose screw type terminals are a practical, low-cost alternative to PC screw type edge connectors, barrier blocks, terminal boards and terminal strips. Steadfast and easy to install, will accommodate solid or stranded wire, crimp-type terminals or lugs. Multi-placement of these low-profile terminals make them ideally suited for high-density packaging. Supplied unassembled or with screw installed and captivated.

PRINCIPAL FEATURES

- Low profile
- Stable, no-rock design with exclusive anti-rotational feature
- Easily mounts with four legs into pre-drilled or punched holes
- Accepts 14-22 AWG solid or stranded wire, crimp-type terminals or lugs
- Ideally suited for high-density packaging
- Available in horizontal or vertical mounting
- Space-saving and time saving
- Easy accessibility for PC board testing
- Binding screw is positioned above board level to avoid wicking during wave soldering
- Terminals are made of Brass with Tin Plate
- Supplied with a combination drive 6-32 binding head screw



HORIZONTAL TYPE

SPECIFICATIONS

Rated: 15 Amps



Terminal:

.032 Thick Brass, Tin Plate

Binding Head Screw:


Brass, Nickel Plate

Mounting Detail



CAT. NO. 7779 (Supplied Less Screw)
 CAT. NO. 7690 (Screw Supplied Unassembled)
 CAT. NO. 7692 (Screw Installed & Captivated)

CAT. NO. 7781 (Supplied Less Screw)
 CAT. NO. 8190 (Screw Supplied Unassembled)
 CAT. NO. 7700 (Screw Installed & Captivated)



VERTICAL TYPE

SPECIFICATIONS

Rated: 15 Amps



Terminal:

.032 Thick Brass, Tin Plate

Binding Head Screw:

Brass, Nickel Plate

Mounting Detail



CAT. NO. 7780 (Supplied Less Screw)
 CAT. NO. 7691 (Screw Supplied Unassembled)
 CAT. NO. 7693 (Screw Installed & Captivated)

CAT. NO. 7782 (Supplied Less Screw)
 CAT. NO. 8191 (Screw Supplied Unassembled)
 CAT. NO. 7701 (Screw Installed & Captivated)

CUSTOM DESIGNS




45° PC MOUNT SCREW TERMINAL

SPECIFICATIONS


Rated: 15 Amps

Terminal: .032 Thick Brass, Tin Plate

Binding Head Screw: Brass, Nickel Plate



Mounting Detail



CAT. NO. 7783 (Supplied Less Screw)
 CAT. NO. 8189 (Screw Supplied Unassembled)
 CAT. NO. 7702 (Screw Installed & Captivated)