

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 805790

2N4403

Preferred Device

General Purpose Transistors

PNP Silicon

Features

- Pb-Free Packages are Available*

MAXIMUM RATINGS

| Rating | Symbol | Value | Unit |
|---|----------------|----------------|----------------------------|
| Collector – Emitter Voltage | V_{CEO} | 40 | Vdc |
| Collector – Base Voltage | V_{CBO} | 40 | Vdc |
| Emitter – Base Voltage | V_{EBO} | 5.0 | Vdc |
| Collector Current – Continuous | I_C | 600 | mAdc |
| Total Device Dissipation @ $T_A = 25^\circ\text{C}$ Derate above 25°C | P_D | 625 5.0 | mW mW/ $^\circ\text{C}$ |
| Total Device Dissipation @ $T_C = 25^\circ\text{C}$ Derate above 25°C | P_D | 1.5 12 | W mW/ $^\circ\text{C}$ |
| Operating and Storage Junction Temperature Range | T_J, T_{stg} | -55 to +150 | $^\circ\text{C}$ |

THERMAL CHARACTERISTICS

| Characteristic | Symbol | Max | Unit |
|---|-----------------|------|---------------------------|
| Thermal Resistance, Junction-to-Ambient | $R_{\theta JA}$ | 200 | $^\circ\text{C}/\text{W}$ |
| Thermal Resistance, Junction-to-Case | $R_{\theta JC}$ | 83.3 | $^\circ\text{C}/\text{W}$ |



Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.




ON Semiconductor®

<http://onsemi.com>



TO-92
CASE 29
STYLE 1

MARKING DIAGRAM



2N4403 = Device Code
A = Assembly Location
Y = Year
WW = Work Week
■ = Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 3 of this data sheet.

Preferred devices are recommended choices for future use and best overall value.

2N4403

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

| Characteristic | Symbol | Min | Max | Unit | |
|--|---|------------------------------|-------------------------|--------------------|----|
| OFF CHARACTERISTICS | | | | | |
| Collector–Emitter Breakdown Voltage (Note 1) (I _C = 1.0 mA _{dc} , I _B = 0) | V _{(BR)CEO} | 40 | – | V _{dc} | |
| Collector–Base Breakdown Voltage (I _C = 0.1 mA _{dc} , I _E = 0) | V _{(BR)CBO} | 40 | – | V _{dc} | |
| Emitter–Base Breakdown Voltage (I _E = 0.1 mA _{dc} , I _C = 0) | V _{(BR)EBO} | 5.0 | – | V _{dc} | |
| Base Cutoff Current (V _{CE} = 35 V _{dc} , V _{EB} = 0.4 V _{dc}) | I _{BEV} | – | 0.1 | μA _{dc} | |
| Collector Cutoff Current (V _{CE} = 35 V _{dc} , V _{EB} = 0.4 V _{dc}) | I _{CEX} | – | 0.1 | μA _{dc} | |
| ON CHARACTERISTICS | | | | | |
| DC Current Gain (I _C = 0.1 mA _{dc} , V _{CE} = 1.0 V _{dc}) (I _C = 1.0 mA _{dc} , V _{CE} = 1.0 V _{dc}) (I _C = 10 mA _{dc} , V _{CE} = 1.0 V _{dc}) (I _C = 150 mA _{dc} , V _{CE} = 2.0 V _{dc}) (Note 1) (I _C = 500 mA _{dc} , V _{CE} = 2.0 V _{dc}) (Note 1) | h _{FE} | 30 60 100 100 20 | – – – 300 – | – | |
| Collector–Emitter Saturation Voltage (Note 1) (I _C = 150 mA _{dc} , I _B = 15 mA _{dc}) (I _C = 500 mA _{dc} , I _B = 50 mA _{dc}) | V _{CE(sat)} | – – | 0.4 0.75 | V _{dc} | |
| Base–Emitter Saturation Voltage (Note 1) (I _C = 150 mA _{dc} , I _B = 15 mA _{dc}) (I _C = 500 mA _{dc} , I _B = 50 mA _{dc}) | V _{BE(sat)} | 0.75 – | 0.95 1.3 | V _{dc} | |
| SMALL–SIGNAL CHARACTERISTICS | | | | | |
| Current–Gain – Bandwidth Product (I _C = 20 mA _{dc} , V _{CE} = 10 V _{dc} , f = 100 MHz) | f _T | 200 | – | MHz | |
| Collector–Base Capacitance (V _{CB} = 10 V _{dc} , I _E = 0, f = 1.0 MHz) | C _{cb} | – | 8.5 | pF | |
| Emitter–Base Capacitance (V _{EB} = 0.5 V _{dc} , I _C = 0, f = 1.0 MHz) | C _{eb} | – | 30 | pF | |
| Input Impedance (I _C = 1.0 mA _{dc} , V _{CE} = 10 V _{dc} , f = 1.0 kHz) | h _{ie} | 1.5 k | 15 k | Ω | |
| Voltage Feedback Ratio (I _C = 1.0 mA _{dc} , V _{CE} = 10 V _{dc} , f = 1.0 kHz) | h _{re} | 0.1 | 8.0 | X 10 ^{–4} | |
| Small–Signal Current Gain (I _C = 1.0 mA _{dc} , V _{CE} = 10 V _{dc} , f = 1.0 kHz) | h _{fe} | 60 | 500 | – | |
| Output Admittance (I _C = 1.0 mA _{dc} , V _{CE} = 10 V _{dc} , f = 1.0 kHz) | h _{oe} | 1.0 | 100 | μmhos | |
| SWITCHING CHARACTERISTICS | | | | | |
| Delay Time | (V _{CC} = 30 V _{dc} , V _{BE} = +2.0 V _{dc} , I _C = 150 mA _{dc} , I _{B1} = 15 mA _{dc}) | t _d | – | 15 | ns |
| Rise Time | | t _r | – | 20 | ns |
| Storage Time | | t _s | – | 225 | ns |
| Fall Time | | t _f | – | 30 | ns |

1. Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2.0%.

2N4403

ORDERING INFORMATION

| Device | Package | Shipping† |
|-------------|--------------------|---------------------|
| 2N4403 | TO-92 | 5,000 Units / Box |
| 2N4403G | TO-92 (Pb-Free) | 5,000 Units / Box |
| 2N4403RL | TO-92 | 2,000 / Tape & Reel |
| 2N4403RLG | TO-92 (Pb-Free) | 2,000 / Tape & Reel |
| 2N4403RLRA | TO-92 | 2,000 / Tape & Reel |
| 2N4403RLRAG | TO-92 (Pb-Free) | 2,000 / Tape & Reel |
| 2N4403RLRM | TO-92 | 2,000 / Ammo Pack |
| 2N4403RLRMG | TO-92 (Pb-Free) | 2,000 / Ammo Pack |
| 2N4403RLRP | TO-92 | 2,000 / Ammo Pack |
| 2N4403RLRPG | TO-92 (Pb-Free) | 2,000 / Ammo Pack |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

SWITCHING TIME EQUIVALENT TEST CIRCUIT




Figure 1. Turn-On Time




Figure 2. Turn-Off Time

TRANSIENT CHARACTERISTICS

— 25°C - - - 100°C




Figure 3. Capacitances




Figure 4. Charge Data




Figure 5. Turn-On Time




Figure 6. Rise Time




Figure 7. Storage Time

SMALL-SIGNAL CHARACTERISTICS
NOISE FIGURE

$V_{CE} = -10$ Vdc, $T_A = 25^\circ\text{C}$; Bandwidth = 1.0 Hz




Figure 8. Frequency Effects




Figure 9. Source Resistance Effects

2N4403

h PARAMETERS

$V_{CE} = -10$ Vdc, $f = 1.0$ kHz, $T_A = 25^\circ\text{C}$

This group of graphs illustrates the relationship between h_{fe} and other "h" parameters for this series of transistors. To obtain these curves, a high-gain and a low-gain unit were

selected from the 2N4403 lines, and the same units were used to develop the correspondingly-numbered curves on each graph.




Figure 10. Current Gain




Figure 11. Input Impedance




Figure 12. Voltage Feedback Ratio




Figure 13. Output Admittance

2N4403

STATIC CHARACTERISTICS




Figure 14. DC Current Gain




Figure 15. Collector Saturation Region




Figure 16. "On" Voltages





Figure 17. Temperature Coefficients

2N4403

PACKAGE DIMENSIONS

TO-92
TO-226AA
CASE 29-11
ISSUE AL




NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

| DIM | INCHES | | MILLIMETERS | |
|-----|--------|-------|-------------|-------|
| | MIN | MAX | MIN | MAX |
| A | 0.175 | 0.205 | 4.45 | 5.20 |
| B | 0.170 | 0.210 | 4.32 | 5.33 |
| C | 0.125 | 0.165 | 3.18 | 4.19 |
| D | 0.016 | 0.021 | 0.407 | 0.533 |
| G | 0.045 | 0.055 | 1.15 | 1.39 |
| H | 0.095 | 0.105 | 2.42 | 2.66 |
| J | 0.015 | 0.020 | 0.39 | 0.50 |
| K | 0.500 | --- | 12.70 | --- |
| L | 0.250 | --- | 6.35 | --- |
| N | 0.080 | 0.105 | 2.04 | 2.66 |
| P | --- | 0.100 | --- | 2.54 |
| R | 0.115 | --- | 2.93 | --- |
| V | 0.135 | --- | 3.43 | --- |

STYLE 1:

1. EMITTER
2. BASE
3. COLLECTOR

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
P.O. Box 61312, Phoenix, Arizona 85082-1312 USA
Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada
Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051
Phone: 81-3-5773-3850

ON Semiconductor Website: <http://onsemi.com>

Order Literature: <http://www.onsemi.com/litorder>

For additional information, please contact your local Sales Representative.