

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039000040](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Jr. Power Connectors](#)  
**Description:** Mini-Fit Male Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass Contact, 18-24 AWG, Reel

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">5558</a>
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Jr. Power Connectors</a>
Packaging Alternative	<a href="#">39000041 (Loose)</a>
Product Name	Mini-Fit
UPC	800753643239

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.123/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Engineering Number	5558T
--------------------	-------



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ECHA\_01\_2020 (16  
January 2020

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[5558 Series](#)

**Use With**

Mini-Fit Jr. Plug Housing [5559](#) <br>Mini-Fit  
BMI Plug Housing [42475](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool	<a href="#">11030044</a>
FineAdjust Applicator	<a href="#">2037026300</a>
for Mini-Fit Double Crimp Applications Using Two 22 AWG Wires	
Hand Crimp Tool	<a href="#">638190901</a>
for Mini-Fit Jr. Male and Female Crimp	

Terminals, 18-24  
 AWG  
 FineAdjust Applicator 639015600  
 for Insulation OD  
 1.90-2.30mm - 18-24  
 AWG  
 FineAdjust Applicator 639023900  
 for Insulation OD  
 1.40-1.70mm - 18-24  
 AWG  
 FineAdjust Applicator 639024800  
 for Insulation OD  
 2.50-2.95mm  
 Optimized for 18  
 AWG Only  
 FineAdjust Applicator 639024900  
 for Insulation OD  
 2.30-2.60mm - 18-24  
 AWG  
 FineAdjust Applicator 639047800  
 for Insulation OD  
 2.50-2.95mm, 18-24  
 AWG  
 FineAdjust Applicator 639048000  
 for Insulation OD  
 1.65-2.05mm, 18-24  
 AWG  
 T2 Terminator 639115600  
 for insulation OD  
 1.90-2.30mm - 18-24  
 AWG  
 T2 Terminator 639123900  
 for insulation OD  
 1.40-1.70mm - 18-24  
 AWG  
 T2 Terminator 639124800  
 for insulation OD  
 2.50-2.95mm  
 optimized for 18  
 AWG only  
 T2 Terminator 639124900  
 for insulation OD  
 2.30-2.60mm - 18-24  
 AWG  
 T2 Terminator 639147800  
 for Mini-Fit Crimp  
 Terminals, 18-24  
 AWG with Large  
 Insulation ODs  
 T2 Terminator 639148000  
 for Mini-Fit Crimp  
 Terminals, 18-24  
 AWG with Smaller  
 Insulation ODs

**Japan**

<b>Description</b>	<b>Product #</b>
S-1 Applicator for Mini-Fit Plug and Receptacle Terminals, 18-24 AWG, UL1007 Wires	<u>570223700</u>
S-1 Applicator for Mini-Fit Plug and Receptacle	<u>570223710</u>

Terminals, 18-24  
AWG, UL1015 Wires  
Hand Extraction Tool [570316000](#)

This document was generated on 03/09/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**