

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000040](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: Mini-Fit® Male Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass Contact, 18-24 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [Test Summary TS-5556-002 \(PDF\)](#)
[Product Specification PS-5556-002 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-5558-001 \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [5558](#)
 Application Power
 Crimp Quality Equipment Yes
 Overview [Mini-Fit Jr.™ Power Connectors](#)
 Packaging Alternative [39-00-0041 \(Loose\)](#)
 Product Name Mini-Fit®
 UPC 800753643239

Physical

Durability (mating cycles max) 30
 Gender Male
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.123/g
 Packaging Type Reel
 Plating min - Mating 0.889µm
 Plating min - Termination 0.889µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.30-3.10mm
 Wire Size AWG 18, 20, 22, 24
 Wire Size mm² N/A

Electrical

Current - Maximum per Contact 9.0A
 Voltage - Maximum 600V

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Old Part Number 5558T

Reference - Drawing Numbers

Packaging Specification [PK-5558-001](#)
 Product Specification [PS-5556-002](#), [RPS-30067-002](#), [RPS-42474-001](#)
 Sales Drawing [SD-5558****](#)
 Test Summary [TS-5556-002](#)



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

No -ED/39/2015 (15 June 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Compliant

Search Parts in this Series

[5558 Series](#)

Mates With

[5556 Mini-Fit® Crimp Terminal](#)

Use With

[5559 Mini-Fit Jr.™ Plug Housing](#), [30068 Mini-Fit® TPA Plug Housing](#), [42475 Mini-Fit® BMI Plug Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

FineAdjust™
Applicator for
Insulation OD

[0639024800](#)

2.50-2.95mm Optimized for 18 AWG Only T2 Terminator™	<u>0639102600</u>
for insulation OD 2.50-2.95mm - 18-24 AWG T2 Terminator™	<u>0639124800</u>
for insulation OD 2.50-2.95mm optimized for 18 AWG only T2 Terminator™	<u>0639124900</u>
for insulation OD 2.30-2.60mm - 18-24 AWG Hand Crimp Tool for	<u>0638190900</u>
Male and Female Crimp Terminals, 16-24 AWG Wire T2 Terminator™ for	<u>0639102900</u>
insulation OD 1.65 – 2.05mm – 18 – 24 AWG T2 Terminator™	<u>0639123900</u>
for insulation OD 1.40-1.70mm - 18-24 AWG Extraction Tool	<u>0011030044</u>
T2 Terminator™	<u>0639115600</u>
for insulation OD 1.90-2.30mm - 18-24 AWG FineAdjust™	<u>0639002600</u>
Applicator for Insulation OD 2.50-2.95mm, 18-24 AWG Wire FineAdjust™	<u>0639002900</u>
Applicator for Insulation OD 1.65-2.05mm, 18-24 AWG Wire FineAdjust™	<u>0639015600</u>
Applicator for Insulation OD 1.90-2.30mm - 18-24 AWG FineAdjust™	<u>0639023900</u>
Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG FineAdjust™	<u>0639024900</u>
Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG Japan	
Description	Product #
Hand Extraction Tool	<u>0570316000</u>

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION