


### General Specification :

- Lead Wire: UL Type  
(+)Red (-)Black
- Operation Temperature :  
Temperature: -10°C~+70°C  
Humidity: 35%~85%RH
- Store Temperature :  
Temperature: -40°C~+70°C  
Humidity: 35%~85%RH

### Motor Protection :

- Impedance Protected
- Reverse Polarity Protected

### Performance Curves



Item No.	Bearing System	Rated Voltage (V DC)	Rated Current (AMP)	Input Power (Watt)	Fan Speed (RPM)	Air Flow (CFM)	Static Pressure (MM-H2O)	Noise Level (dBA)	Dimension (mm)
CC4010L05S CC4010L05B CC4010L05D CC4010L05SH	Sleeve 1-Ball 2-Ball Hydraulic	5V	0.11	0.55	4,000 ± 10%	3.60	1.40	21	40 X 40 X 10
CC4010M05S CC4010M05B CC4010M05D CC4010M05SH	Sleeve 1-Ball 2-Ball Hydraulic	5V	0.13	0.65	5,000 ± 10%	5.60	2.60	23	40 X 40 X 10
CC4010H05S CC4010H05B CC4010H05D CC4010H05SH	Sleeve 1-Ball 2-Ball Hydraulic	5V	0.16	0.80	6,000 ± 10%	6.80	3.60	27	40 X 40 X 10
CC4010L12S CC4010L12B CC4010L12D CC4010L12SH	Sleeve 1-Ball 2-Ball Hydraulic	12V	0.05	0.60	4,000 ± 10%	3.60	1.40	21	40 X 40 X 10
CC4010M12S CC4010M12B CC4010M12D CC4010M12SH	Sleeve 1-Ball 2-Ball Hydraulic	12V	0.06	0.72	5,000 ± 10%	5.60	2.60	23	40 X 40 X 10
CC4010H12S CC4010H12B CC4010H12D CC4010H12SH	Sleeve 1-Ball 2-Ball Hydraulic	12V	0.07	0.84	6,000 ± 10%	6.80	3.60	27	40 X 40 X 10
CC4010L24S CC4010L24B CC4010L24D CC4010L24SH	Sleeve 1-Ball 2-Ball Hydraulic	24V	0.04	0.96	4,000 ± 10%	3.60	1.40	21	40 X 40 X 10
CC4010M24S CC4010M24B CC4010M24D CC4010M24SH	Sleeve 1-Ball 2-Ball Hydraulic	24V	0.05	1.20	5,000 ± 10%	5.60	2.60	23	40 X 40 X 10
CC4010H24S CC4010H24B CC4010H24D CC4010H24SH	Sleeve 1-Ball 2-Ball Hydraulic	24V	0.06	1.44	6,000 ± 10%	6.80	3.60	27	40 X 40 X 10