


ENERGIZER NO. 412



Industry Standard Dimensions in mm (inches)



Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)

Designation: ANSI / NEDA-215, IEC-15F20

Battery Voltage: 22.5 Volts

Average Weight: 38 grams (1.3 oz.)

Volume: 21 cubic centimeters (1.3 cubic inch)


Average Capacity: 140 mAh to 0.8 volts/cell
 (Rated at 25 mA continuous drain at 21°C)

Cells: Fifteen No. 112 in series

Jacket: Metal

TYPICAL DISCHARGE CURVE

Simulated Test @ 21°C (70°F)



Simulated Application Test
 Estimated Average Service at 21°C (70°F)

Schedule:	Typical Drains at 18V (milliamperes)	Load (ohms)	Cutoff Voltage					
			12V	13.5V	15V	16.5V	18V	19.5V
4 hours/day	0.8	22,500	209	197	184	167	134	55

Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. Inc. - All Rights Reserved