

Solid Tantalum Surface Mount Capacitors TANTAMOUNT[®], Molded Case, Low ESR



Effective September 2005, new capacitor ratings will not be added to the 593D series. All new ratings are available in the TR3 series. The TR3 series offers state-of-the-art low ESR for switch Mode Power Supplies and DC/DC Converters.

FEATURES

- Terminations: 100 % matte tin, standard, tin/lead available
- Compliant terminations
- Molded case available in five case codes
- Compatible with "High Volume" automatic pick and place equipment
- High ripple current carrying capability
- Low ESR
- Meets IEC specification QC300801/US0001 and EIA535BAAC mechanical and performance requirements
- Compliant to RoHS directive 2002/95/EC



RoHS*
COMPLIANT

PERFORMANCE/ELECTRICAL CHARACTERISTICS

Operating Temperature: - 55 °C to + 125 °C

Note: Refer to Doc. 40088

Capacitance Range: 0.47 μ F to 680 μ F

Capacitance Tolerance: \pm 5 %, \pm 10 %, \pm 20 %

100 % Surge Current Tested (B, C, D and E Case Sizes)

Voltage Rating: 4 VDC to 50 VDC

ORDERING INFORMATION					
593D TYPE	107 CAPACITANCE	X9 CAPACITANCE TOLERANCE	010 DC VOLTAGE RATING AT +85 °C	D CASE CODE	2WE3 TERMINATION AND PACKAGING
This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow	X0 = \pm 20 % X9 = \pm 10 % X5 = \pm 5 %	This is expressed in volts. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V)	See Ratings and Case Codes Table	2TE3: Matte tin, 7" (178 mm) reel 2WE3: Matte tin, 13" (330 mm) reel 8T: Tin/lead, 7" (178 mm) reel 8W: Tin/lead, 13" (330 mm) reel	

Note

We reserve the right to supply higher voltage ratings and tighter capacitance tolerance capacitors in the same case size.

Voltage substitutions will be marked with the higher voltage rating.

Effective July 15, 2008, part numbers with solderable termination codes 2T and 2W may have either matte or tin/lead terminations. Codes 2TE3 and 2WE3 specify only matte tin terminations. Codes 8T and 8W specify only tin/lead terminations.

DIMENSIONS in inches [millimeters]							
CASE CODE	EIA SIZE	L	W	H	P	Tw	TH (MIN.)
A	3216-18	0.126 \pm 0.008 [3.2 \pm 0.20]	0.063 \pm 0.008 [1.6 \pm 0.20]	0.063 \pm 0.008 [1.6 \pm 0.20]	0.031 \pm 0.012 [0.80 \pm 0.30]	0.047 \pm 0.004 [1.2 \pm 0.10]	0.028 [0.70]
B	3528-21	0.138 \pm 0.008 [3.5 \pm 0.20]	0.110 \pm 0.008 [2.8 \pm 0.20]	0.075 \pm 0.008 [1.9 \pm 0.20]	0.031 \pm 0.012 [0.80 \pm 0.30]	0.087 \pm 0.004 [2.2 \pm 0.10]	0.028 [0.70]
C	6032-28	0.236 \pm 0.012 [6.0 \pm 0.30]	0.126 \pm 0.012 [3.2 \pm 0.30]	0.098 \pm 0.012 [2.5 \pm 0.30]	0.051 \pm 0.012 [1.3 \pm 0.30]	0.087 \pm 0.004 [2.2 \pm 0.10]	0.039 [1.0]
D	7343-31	0.287 \pm 0.012 [7.3 \pm 0.30]	0.170 \pm 0.012 [4.3 \pm 0.30]	0.110 \pm 0.012 [2.8 \pm 0.30]	0.051 \pm 0.012 [1.3 \pm 0.30]	0.095 \pm 0.004 [2.4 \pm 0.10]	0.039 [1.0]
E	7343-43	0.287 \pm 0.012 [7.3 \pm 0.30]	0.170 \pm 0.012 [4.3 \pm 0.30]	0.158 \pm 0.012 [4.0 \pm 0.30]	0.051 \pm 0.012 [1.3 \pm 0.30]	0.095 \pm 0.004 [2.4 \pm 0.10]	0.039 [1.0]

* Pb containing terminations are not RoHS compliant, exemptions may apply

RATINGS AND CASE CODES								
μF	4 V	6.3 V	10 V	16 V	20 V	25 V	35 V	50 V
0.47							A	
0.68							A	
1.0					A	A	A/B	B/C
1.5						A	B/C	B/C
2.2					A	A/B	B/C	C/D
3.3				A	A	B	C	C/D
4.7			A	A/B	A/B	B/C	C	E/D
6.8			A	A	B	C	C/D	D/E
10		A	A	A/B/C	B/C	C	C/D	D/E
15	A	A	A/B	B/C	B/C	C/D	D/E	
22	A	A/B	A/B/C	B/C	C/D	D	D/E	
33	A/B	A/B	B/C	B/C/D	C/D	D/E		
47	A/B	B/C	B/C/D	C/D	D/E	E		
68	B/C	B/C	C/D	D	D/E			
100	B/C	B/C/D	C/D	D/E	E			
150	B/C/D	C/D/E	D/E	E				
220	C/D	D/E	D/E					
330	D	D/E	E					
470	D/E	E						
680	E							

MARKING		
<p style="text-align: center;">"A" Case Size</p>	"A" CASE VOLTAGE CODE	
	VOLTS	CODE
	4.0	G
	6.3	J
	10	A
	16	C
	20	D
25	E	
35	V	
50	T	
<p style="text-align: center;">"B, C, D, E, V" Case Sizes</p>		

Marking:

Capacitor marking includes an anode (+) polarity band, capacitance in microfarads and the voltage rating. "A" Case capacitors use a letter code for the voltage and EIA capacitance code.

The Vishay Sprague[®] trademark is included if space permits. Capacitors rated at 6.3 V are marked 6 V.

A manufacturing date code is marked on all capacitors.

Capacitors might bear a slightly different marking than the one shown above. For example, rating 22 μF 10 V could be marked either as 22-10L or 22R10.

Call the factory for further explanation.



Solid Tantalum Surface Mount Capacitors
TANTAMOUNT[®], Molded Case, Low ESR

Vishay Sprague

RATINGS AND PART NUMBER REFERENCE						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{rms} (A)
4 VDC AT + 85 °C, 2.7 VDC AT + 125 °C						
15	A	593D156(1)004A2(2)	0.6	6	1.500	0.22
22	A	593D226(1)004A2(2)	0.9	6	1.500	0.22
33	A	593D336(1)004A2(2)	1.3	6	1.500	0.22
33	B	593D336(1)004B2(2)	1.3	6	0.500	0.41
47	A	593D476(1)004A2(2)	1.9	14	0.800	0.31
47	B	593D476(1)004B2(2)	1.9	6	0.500	0.41
68	B	593D686(1)004B2(2)	2.7	6	0.500	0.41
68	C	593D686(1)004C2(2)	2.7	6	0.275	0.63
100	B	593D107(1)004B2(2)	4.0	8	0.450	0.43
100	C	593D107(1)004C2(2)	4.0	6	0.225	0.66
150	B	593D157(1)004B2(2)	6.0	14	0.500	0.41
150	C	593D157(1)004C2(2)	6.0	12	0.250	0.66
150	D	593D157(1)004D2(2)	6.0	8	0.150	1.00
220	C	593D227(1)004C2(2)	8.8	8	0.200	0.74
220	D	593D227(1)004D2(2)	8.8	8	0.150	1.00
330	D	593D337(1)004D2(2)	13.2	8	0.150	1.00
470	D	593D477(1)004D2(2)	18.8	10	0.125	1.10
470	E	593D477(1)004E2(2)	18.8	10	0.100	1.28
680	E	593D687(1)004E2(2)	27.2	12	0.100	1.28
6.3 VDC AT + 85 °C, 4 VDC AT 125 °C						
10	A	593D106(1)6R3A2(2)	0.6	6	2.000	0.19
15	A	593D156(1)6R3A2(2)	0.9	6	2.000	0.19
22	A	593D226(1)6R3A2(2)	1.3	6	2.000	0.19
22	B	593D226(1)6R3B2(2)	1.3	6	0.600	0.38
33	A	593D336(1)6R3A2(2)	2.0	14	0.800	0.31
33	B	593D336(1)6R3B2(2)	2.0	6	0.600	0.38
47	B	593D476(1)6R3B2(2)	2.8	6	0.550	0.39
47	C	593D476(1)6R3C2(2)	2.8	6	0.300	0.61
68	B	593D686(1)6R3B2(2)	4.1	6	0.550	0.39
68	C	593D686(1)6R3C2(2)	4.1	6	0.275	0.63
100	B	593D107(1)6R3B2(2)	6.0	15	0.500	0.41
100	C	593D107(1)6R3C2(2)	6.0	6	0.250	0.66
100	D	593D107(1)6R3D2(2)	6.0	6	0.140	1.04
150	C	593D157(1)6R3C2(2)	9.0	8	0.200	0.74
150	D	593D157(1)6R3D2(2)	9.0	8	0.125	1.10
150	E	593D157(1)6R3E2(2)	9.0	8	0.100	1.28
220	D	593D227(1)6R3D2(2)	13.2	8	0.100	1.22
220	E	593D227(1)6R3E2(2)	13.2	8	0.100	1.28
330	D	593D337(1)6R3D2(2)	19.8	8	0.125	1.10
330	E	593D337(1)6R3E2(2)	19.8	8	0.100	1.28
470	E	593D477(1)6R3E2(2)	28.2	10	0.100	1.28
10 VDC AT + 85 °C, 7 VDC AT 125 °C						
4.7	A	593D475(1)010A2(2)	0.5	6	3.000	0.16
6.8	A	593D685(1)010A2(2)	0.7	6	3.000	0.16
10	A	593D106(1)010A2(2)	1.0	6	2.000	0.19
15	A	593D156(1)010A2(2)	1.5	6	2.000	0.19
15	B	593D156(1)010B2(2)	1.5	6	0.700	0.35
22	A	593D226(1)010A2(2)	2.2	8	1.500	0.22
22	B	593D226(1)010B2(2)	2.2	6	0.700	0.35
22	C	593D226(1)010C2(2)	2.2	6	0.345	0.56
33	B	593D336(1)010B2(2)	3.3	6	0.600	0.38
33	C	593D336(1)010C2(2)	3.3	6	0.300	0.61

Notes

- (1) Tolerance: X0, X9, X5
- (2) Terminations and packaging: 2TE3, 2WE3, 8T, 8W

RATINGS AND PART NUMBER REFERENCE						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{rms} (A)
10 VDC AT + 85 °C, 7 VDC AT 125 °C						
47	B	593D476(1)010B2(2)	4.7	6	0.600	0.38
47	C	593D476(1)010C2(2)	4.7	6	0.300	0.61
47	D	593D476(1)010D2(2)	4.7	6	0.200	0.87
68	C	593D686(1)010C2(2)	6.8	6	0.275	0.63
68	D	593D686(1)010D2(2)	6.8	6	0.150	1.00
100	C	593D107(1)010C2(2)	10.0	8	0.200	0.74
100	D	593D107(1)010D2(2)	10.0	6	0.100	1.22
150	D	593D157(1)010D2(2)	15.0	8	0.100	1.22
150	E	593D157(1)010E2(2)	15.0	8	0.100	1.28
220	D	593D227(1)010D2(2)	22.0	8	0.125	1.10
220	E	593D227(1)010E2(2)	22.0	8	0.100	1.28
330	E	593D337(1)010E2(2)	33.0	10	0.100	1.28
16 VDC AT + 85 °C, 10 VDC AT + 125 °C						
3.3	A	593D335(1)016A2(2)	0.5	6	3.500	0.15
4.7	A	593D475(1)016A2(2)	0.8	6	2.500	0.17
4.7	B	593D475(1)016B2(2)	0.8	6	1.500	0.24
6.8	A	593D685(1)016A2(2)	1.1	6	3.000	0.16
10	A	593D106(1)016A2(2)	1.6	6	1.700	0.21
10	B	593D106(1)016B2(2)	1.6	6	0.800	0.33
10	C	593D106(1)016C2(2)	1.6	6	0.450	0.49
15	B	593D156(1)016B2(2)	2.4	6	0.800	0.33
15	C	593D156(1)016C2(2)	2.4	6	0.400	0.52
22	B	593D226(1)016B2(2)	3.5	6	0.700	0.35
22	C	593D226(1)016C2(2)	3.5	6	0.350	0.56
33	B	593D336X0016B2(2)	5.3	6	0.700	0.35
33	C	593D336(1)016C2(2)	5.3	6	0.300	0.61
33	D	593D336(1)016D2(2)	4.2	4	0.225	0.82
47	C	593D476(1)016C2(2)	7.5	6	0.300	0.61
47	D	593D476(1)016D2(2)	7.5	6	0.150	1.00
68	D	593D686(1)016D2(2)	10.9	6	0.150	1.00
100	D	593D107(1)016D2(2)	16.0	8	0.125	1.10
100	E	593D107(1)016E2(2)	16.0	8	0.100	1.28
150	E	593D157(1)016E2(2)	24.0	8	0.100	1.28
20 VDC AT + 85 °C, 13 VDC AT + 125 °C						
1.0	A	593D105(1)020A2(2)	0.5	4	5.500	0.12
2.2	A	593D225(1)020A2(2)	0.5	6	4.000	0.14
3.3	A	593D335(1)020A2(2)	0.7	6	4.000	0.14
4.7	A	593D475(1)020A2(2)	0.9	6	3.500	0.15
4.7	B	593D475(1)020B2(2)	0.9	6	1.000	0.29
6.8	B	593D685(1)020B2(2)	1.4	6	1.000	0.29
10	B	593D106(1)020B2(2)	2.0	6	1.000	0.29
10	C	593D106(1)020C2(2)	2.0	6	0.450	0.49
15	B	593D156(1)020B2(2)	3.0	6	1.000	0.29
15	C	593D156(1)020C2(2)	3.0	6	0.400	0.52
22	C	593D226(1)020C2(2)	4.4	6	0.375	0.54
22	D	593D226(1)020D2(2)	3.5	4	0.225	0.82
33	C	593D336(1)020C2(2)	6.6	6	0.350	0.56
33	D	593D336(1)020D2(2)	6.6	6	0.200	0.87
47	D	593D476(1)020D2(2)	9.4	6	0.200	0.87
47	E	593D476(1)020E2(2)	7.5	4	0.150	1.05
68	D	593D686(1)020D2(2)	13.6	6	0.175	0.93
68	E	593D686(1)020E2(2)	13.6	6	0.150	1.05
100	E	593D107(1)020E2(2)	20.0	8	0.150	1.05

Notes

- (1) Tolerance: X0, X9, X5
- (2) Terminations and packaging: 2TE3, 2WE3, 8T, 8W



Solid Tantalum Surface Mount Capacitors
TANTAMOUNT[®], Molded Case, Low ESR

Vishay Sprague

RATINGS AND PART NUMBER REFERENCE						
CAPACITANCE (μF)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μA)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I _{rms} (A)
25 VDC AT + 85 °C, 17 VDC AT + 125 °C						
1.0	A	593D105(1)025A2(2)	0.5	4	4.000	0.14
1.5	A	593D155(1)025A2(2)	0.5	6	4.000	0.14
2.2	A	593D225(1)025A2(2)	0.6	6	4.000	0.14
2.2	B	593D225(1)025B2(2)	0.6	6	1.500	0.24
3.3	B	593D335(1)025B2(2)	0.8	6	1.500	0.24
4.7	B	593D475(1)025B2(2)	1.2	6	1.500	0.24
4.7	C	593D475(1)025C2(2)	1.2	6	0.525	0.46
6.8	C	593D685(1)025C2(2)	1.7	6	0.500	0.47
10	C	593D106(1)025C2(2)	2.5	6	0.450	0.49
15	C	593D156(1)025C2(2)	3.8	6	0.425	0.51
15	D	593D156(1)025D2(2)	3.8	6	0.250	0.77
22	D	593D226(1)025D2(2)	5.5	6	0.200	0.87
33	D	593D336(1)025D2(2)	8.3	6	0.200	0.87
33	E	593D336(1)025E2(2)	8.3	6	0.200	0.91
47	E	593D476(1)025E2(2)	11.8	6	0.200	0.91
35 VDC AT + 85 °C, 23 VDC AT + 125 °C						
0.47	A	593D474(1)035A2(2)	0.5	4	4.000	0.14
0.68	A	593D684(1)035A2(2)	0.5	4	4.000	0.14
1.0	A	593D105(1)035A2(2)	0.5	4	4.000	0.14
1.0	B	593D105(1)035B2(2)	0.5	4	2.000	0.21
1.5	B	593D155(1)035B2(2)	0.5	6	2.000	0.21
1.5	C	593D155(1)035C2(2)	0.5	6	0.900	0.35
2.2	B	593D225(1)035B2(2)	0.8	6	2.000	0.21
2.2	C	593D225(1)035C2(2)	0.8	6	0.900	0.40
3.3	C	593D335(1)035C2(2)	1.2	6	0.700	0.45
4.7	C	593D475(1)035C2(2)	1.6	6	0.500	0.47
6.8	C	593D685(1)035C2(2)	2.4	6	0.475	0.48
6.8	D	593D685(1)035D2(2)	2.4	6	0.300	0.71
10	C	593D106(1)035C2(2)	3.5	6	0.450	0.49
10	D	593D106(1)035D2(2)	3.5	6	0.300	0.71
15	D	593D156(1)035D2(2)	5.3	6	0.300	0.71
15	E	593D156(1)035E2(2)	5.3	6	0.300	0.74
22	D	593D226(1)035D2(2)	7.7	6	0.300	0.71
22	E	593D226(1)035E2(2)	7.7	6	0.275	0.77
50 VDC AT + 85 °C, 33 VDC AT + 125 °C						
1.0	B	593D105(1)050B2(2)	0.5	4	2.000	0.21
1.0	C	593D105(1)050C2(2)	0.5	4	1.600	0.26
1.5	B	593D155(1)050B2(2)	0.8	6	2.000	0.21
1.5	C	593D155(1)050C2(2)	0.8	6	1.500	0.27
2.2	C	593D225(1)050C2(2)	1.1	6	1.500	0.27
2.2	D	593D225(1)050D2(2)	1.1	6	0.800	0.43
3.3	C	593D335(1)050C2(2)	1.7	6	1.500	0.27
3.3	D	593D335(1)050D2(2)	1.7	6	0.800	0.43
4.7	D	593D475(1)050D2(2)	2.4	6	0.600	0.50
4.7	E	593D475(1)050E2(2)	1.9	6	0.600	0.50
6.8	D	593D685(1)050D2(2)	3.4	6	0.600	0.50
6.8	E	593D685(1)050E2(2)	3.4	6	0.550	0.55
10	D	593D106(1)050D2(2)	5.0	6	0.550	0.52
10	E	593D106(1)050E2(2)	5.0	6	0.550	0.55

Notes

- (1) Tolerance: X0, X9, X5
- (2) Terminations and packaging: 2TE3, 2WE3, 8T, 8W



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.