

CATALOG
Cross Reference

[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)



- ➔ [Part Number Search](#)
- ➔ [Document Search](#)
- ➔ [Product Type Search](#)
- ➔ [Product Family Search](#)
- ➔ [Alphabetical Search](#)
- ➔ [RoHS/ELV Compliance & Alternates](#)
- ➔ [CAD Model Search](#)
- ➔ [Brand Search](#)
- ➔ [Tool Search](#)
- ➔ [Multiple Part Comparison](#)
- ➔ [Lead Free Solutions](#)
- ➔ [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Subminiature and Microminiature D Connectors

↳ Standard Board Mount Connectors


747836-6

[Active](#)

(Corporate P/N: 747836-6)

[Not ELV or RoHS Compliant](#)

[Search for Compliant \(RoHS/ELV\)](#)

[Alternates](#)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ➤ General Info ➤ Sales Info ➤ Assembly Subcontractors 	<ul style="list-style-type: none"> ➤ Pricing & Availability 	<ul style="list-style-type: none"> ➤ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Wave solder capable to 240°C, Wave solder capable to 265°C
Number of Positions:	9
Gender:	Receptacle
PCB Mount Angle:	Right Angle
Product Series:	HD 20
Mating Connector Lock:	With
Mating Connector Lock Type:	Female Screwlocks, Fixed

Other Properties:

Sealed:	No
Application:	Standard
Profile:	Standard
Post Size (mm [in]):	0.66 [.026]
Contact Shape:	Round
Mounting Hole Diameter (mm [in]):	3.18 [.125]
Housing Material:	Thermoplastic
Contact Material:	Phosphor Bronze
Shell Material:	Steel
Shell Plating:	Tin
Housing Flammability Rating:	UL 94V-0
Boardlock Material:	Copper Alloy

<u>PCB Retention Feature:</u>	With
<u>PCB Retention Method Feature:</u>	Boardlocks
<u>Shell Type:</u>	Front Metal Shell
<u>Shell Size:</u>	1
<u>Panel Attachment:</u>	No
<u>Grounding Clips:</u>	Without
<u>Footprint (mm [in]):</u>	14.99 [.590]
<u>Termination Post Length (mm [in]):</u>	3.18 [0.125]
<u>PCB Thickness (in [mm]):</u>	0.062 [1.57]
<u>Contact Mating Area Plating:</u>	Gold (30)
<u>Solder Tail Plating:</u>	Tin-Lead over Nickel
<u>Grounding Indents:</u>	Without
<u>Grounding Straps:</u>	With
<u>PCB Mount Style:</u>	Thru Hole
<u>Color Code:</u>	None
<u>Region:</u>	Americas

<u>Boardlock Plating:</u>	Tin-lead
<u>Female Screwlock Material:</u>	Zinc
<u>Female Screwlock Plating:</u>	Clear Chromate
<u>Eyelet Material:</u>	Brass
<u>Eyelet Plating:</u>	Tin
<u>Comment:</u>	All receptacles are preloaded with size 20 DF posted socket contacts

[Copyright](#) and [Privacy Statement](#)
 Visit [Tyco International Ltd.](#)

[\[Products | Catalog | Brands | Industries | Commerce | Supplier | Contact Us | About | Home \]](#)