

CERAMIC SMD MICRO MINIATURE MICROPROCESSOR CRYSTAL



ABM7

6.0 x 3.3 x 1.3mm

ABM7

Pb in Glass

(exempt per RoHS 2002/95/EC Annex (5))

RoHS
Compliant

FEATURES:

- Low in height (1.3 mm max.)
- Ceramic package assures high reliability
- Small size SMD, suitable for high density applications
- Superior heat-resistant glass sealing
- Wide operating temperature available

APPLICATIONS:

- Computers, Modems, Communication equipment
- Thin equipment
- Industrial wide temperature applications

STANDARD SPECIFICATIONS:


PARAMETERS	
ABRACON P/N	ABM7 Series
Frequency Range	8.00 MHz to 50.00 MHz (*)
Operation Mode	8MHz to 39.999999MHz (Fundamental AT-cut) (Standard) 40MHz to 50MHz (Fundamental AT cut) (See option) 40MHz to 80MHz (3rd OT AT cut) (Standard)
Operating Temperature	-10°C to + 60°C (see options)
Storage Temperature	- 40°C to + 85°C
Frequency Tolerance at +25°C	± 50 ppm max. (see options)
Frequency Stability over the Operating Temp. (Ref to +25°C)	± 50 ppm max. (see options)
Equivalent Series Resistance	See Table 1
Shunt Capacitance C ₀	7pF max.
Load Capacitance C _L	18pF (see options)
Drive Level	100 µW max., 10µW typical
Aging at 25°C First Year	± 5ppm max.
Insulation Resistance	500 MΩ min. with 100Vdc

TABLE 1

Frequency (MHz)	ESR (Ω)	Frequency (MHz)	ESR (Ω)
8.000 - 9.999 (Fund.)	80	16.000 - 50.000 (Fund.)	50
10.000 - 15.999 (Fund.)	60	40.000 - 80.000 (3rd OT)	70


(*) Frequency above 40MHz based on availability. Please contact ABRACON

OPTIONS AND PART IDENTIFICATION (Left blank if standard)



(*) -10°C to +60°C only.
(**) Contact ABRACON for availability for -40°C to +85°C

ABRACON IS
ISO 9001 / QS 9000
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale **Revised: 02.01.10**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

