

FEATURES


1. Reduced package size

Lower surface has been reduced 60% and mounting space 40% compared to conventional 4-pin SOP type.

2. Two types are available: A type with greatly reduced ON resistance, and a type with even lower output capacitance between terminals.

	AQY221R2V (R Type)	AQY221N2V (C Type)
Output capacitance (C)	12.5pF	1.0pF
ON resistance (R)	0.75Ω	9.5Ω

3. Mounting space has been reduced and output signals have been improved by using new flat lead terminals.




4. High speed switching (Part No.: AQY221N2V)

Turn on time: 0.02ms
Turn off time: 0.02ms


TYPICAL APPLICATIONS

Measuring and testing equipment

- Test equipment
IC tester, Liquid crystal driver tester, semiconductor performance tester
- Board tester
Bare board tester, In-circuit tester, function tester
- Medical equipment
Ultrasonic wave diagnostic machine
- Multi-point recorder
Strainmeter, thermo couple



mm inch



TYPES

Type		Output rating*		Part No. (Tape and reel packing style)		Packing quantity
		Load voltage	Load current	Picked from the 1/4-pin side	Picked from the 2/3-pin side	
AC/DC type	Low on resistance (R Type)	40 V	250 mA	AQY221R2VY	AQY221R2VW	Tape and reel: 3,500 pcs.
	Low capacitance (C Type)	40 V	120 mA	AQY221N2VY	AQY221N2VW	

* Indicate the peak AC and DC values.

Notes: (1) Tape package is the standard packing style.

(2) For space reasons, the initial letters of the product number "AQY", the package type indicator "Y" and "W" are omitted from the seal.
(Ex. the label for product number AQY221N2V is 221N2)

RATING

1. Absolute maximum ratings (Ambient temperature: 25°C 77°F)

Item		Symbol	AQY221R2V	AQY221N2V	Remarks
Input	LED forward current	I _F	50mA		
	LED reverse voltage	V _R	5V		
	Peak forward current	I _{FP}	1A		f=100 Hz, Duty factor=0.1%
	Power dissipation	P _{in}	75mW		
Output	Load voltage (peak AC)	V _L	40V		See "CAUTIONS FOR USE" on page 6
	Continuous load current (peak AC)	I _L	0.25A	0.12A	Peak AC, DC
	Peak load current	I _{peak}	0.75A	0.3A	100 ms (1 shot), V _L = DC
	Power dissipation	P _{out}	250mW		
Total power dissipation		P _T	300mW		
I/O isolation voltage		V _{iso}	1,500V AC		
Temperature limits	Operating	T _{opr}	-40°C to +85°C -40°F to +185°F		Non-condensing at low temperatures
	Storage	T _{stg}	-40°C to +100°C -40°F to +212°F		


2. Electrical characteristics (Ambient temperature: 25°C 77°F)

Item		Symbol	AQY221R2V	AQY221N2V	Condition*2	
Input	LED operate current	Typical	0.9 mA	1.0 mA	C type (I _L = 80 mA) R type (I _L = 250 mA)	
		Maximum	3.0 mA			
	LED turn off current	Minimum	0.1 mA	0.2 mA	C type (I _L = 80 mA) R type (I _L = 250 mA)	
		Typical	0.8 mA	0.9 mA		
LED dropout voltage	Typical	1.14 V (1.35 V at I _F = 50mA)		C type (I _F = 5mA) R type (I _F = 5mA)		
	Maximum	1.5 V				
Output	On resistance	Typical	0.75Ω	9.5Ω	C type (I _F = 5mA, I _L = 80 mA Within 1 s on time) R type (I _F = 5mA, I _L = 250 mA Within 1 s on time)	
		Maximum	1.25Ω	12.5Ω		
	Output capacitance	Typical	12.5 pF	1.0 pF	I _F = 0mA V _B = 0 V f = 1 MHz	
		Maximum	18 pF	1.5 pF		
	Off state leakage current	Typical	0.02 nA	0.01 nA	C type (I _F = 0mA, V _L = Max.) R type (I _F = 0mA, V _L = Max.)	
		Maximum	10 nA			
Transfer characteristics	Switching speed	Turn on time*1	Typical	0.10 ms	0.02 ms	C type (I _F = 5mA, V _L = 10V R _L = 125Ω) R type (I _F = 5mA, V _L = 10V R _L = 40Ω)
			Maximum	0.5ms		
		Turn off time*1	Typical	0.02ms		C type (I _F = 5mA, V _L = 10V R _L = 125Ω) R type (I _F = 5mA, V _L = 10V R _L = 40Ω)
			Maximum	0.08 ms	0.2 ms	
	I/O capacitance	Typical	0.8 pF		C type (f = 1MHz, V _B = 0V) R type (f = 1MHz, V _B = 0V)	
		Maximum	1.5 pF			
	Initial I/O isolation resistance	Minimum	R _{iso}	1,000MΩ		500V DC

Notes: 1. For type of connection, see Page 6

2. Variation possible through combinations of output capacitance and ON resistance.

*1 Turn on/Turn off time




*2 Low on resistance (R type)
Low capacitance (C type)


REFERENCE DATA

1. Load current vs. ambient temperature characteristics

Allowable ambient temperature: -40°C to +85°C
-40°F to +185°F




2. Load current vs. Load voltage characteristics
Ambient temperature: 25°C 77°F



3. On resistance vs. ambient temperature characteristics


Measured portion: between terminals 3 and 4
LED current: 5 mA; Load voltage: Max. (DC);
Load current: 250mA (DC) R type, 80mA (DC) C type



AQY2


4. Turn on time vs. ambient temperature characteristics

Measured portion: between terminals 3 and 4
LED current: 5 mA; Load voltage: 10V (DC);
Continuous load current: 250mA (DC) R type,
80mA (DC) C type




5. Turn off time vs. ambient temperature characteristics

Measured portion: between terminals 3 and 4
LED current: 5 mA; Load voltage: 10V (DC);
Continuous load current: 250mA (DC) R type,
80mA (DC) C type




6. LED operate current vs. ambient temperature characteristics

Measured portion: between terminals 3 and 4
LED current: 5 mA; Load voltage: Max. (DC);
Continuous load current: 250mA (DC) R type,
80mA (DC) C type




7. LED turn off current vs. ambient temperature characteristics

Measured portion: between terminals 3 and 4
LED current: 5 mA; Load voltage: Max. (DC);
Continuous load current: 250mA (DC) R type,
80mA (DC) C type




8. LED dropout voltage vs. ambient temperature characteristics

LED current: 5 to 50 mA




9. Voltage vs. current characteristics of output at MOS portion

Measured portion: between terminals 3 and 4
Ambient temperature: 25°C 77°F




10. Off state leakage current

Measured portion: between terminals 3 and 4
Ambient temperature: 25°C 77°F




11. LED forward current vs. turn on time characteristics

Measured portion: between terminals 3 and 4
Load voltage: 10V (DC);
Continuous load current: 250mA (DC) R type,
80mA (DC) C type; Ambient temperature: 25°C 77°F




12. LED forward current vs. turn off time characteristics

Measured portion: between terminals 3 and 4
Load voltage: 10V (DC);
Continuous load current: 250mA (DC) R type,
80mA (DC) C type; Ambient temperature: 25°C 77°F




13. Applied voltage vs. output capacitance characteristics

Measured portion: between terminals 3 and 4
 Frequency: 1 MHz, 30m Vrms;
 Ambient temperature: 25°C 77°F




14. Isolation characteristics (50Ω impedance)

Measured portion: between terminals 3 and 4
 Ambient temperature: 25°C 77°F




15. Insertion loss characteristics (50Ω impedance)

Measured portion: between terminals 3 and 4
 Ambient temperature: 25°C 77°F




16-(1). On resistance distribution (R type)

Measured portion: between terminals 3 and 4
 Continuous load current: 250mA (DC)
 Ambient temperature: 25°C 77°F




16-(2). On resistance distribution (C type)

Measured portion: between terminals 3 and 4
 Continuous load current: 80mA (DC)
 Ambient temperature: 25°C 77°F




17-(1). Turn on time distribution (R type)

Load voltage: 10V (DC)
 Continuous load current: 250mA (DC)
 Ambient temperature: 25°C 77°F




17-(2). Turn on time distribution (C type)

Load voltage: 10V (DC)
 Continuous load current: 80mA (DC)
 Ambient temperature: 25°C 77°F




18-(1). Turn off time distribution (R type)

Load voltage: 10V (DC)
 Continuous load current: 250mA (DC)
 Ambient temperature: 25°C 77°F




18-(2). Turn off time distribution (C type)

Load voltage: 10V (DC)
 Continuous load current: 80mA (DC)
 Ambient temperature: 25°C 77°F




19-(1). LED operate current distribution (R type)


Load voltage: 10V (DC)
 Continuous load current: 250mA (DC)
 Ambient temperature: 25°C 77°F




19-(2). LED operate current distribution (C type)

Load voltage: 10V (DC)
 Continuous load current: 80mA (DC)
 Ambient temperature: 25°C 77°F







Recommended mounting pad (TOP VIEW)



Tolerance: $\pm 0.1 \pm 0.004$



Terminal thickness = 0.15 ± 0.006
General tolerance: $\pm 0.1 \pm 0.004$

SCHEMATIC AND WIRING DIAGRAMS

E₁: Power source at input side; V_{IN}: Input voltage; I_F: LED forward current; I_{IN}: Input current; V_L: Load voltage; I_L: Load current

Schematic	Output configuration	Load	Wiring diagram
	1a	AC/DC	

CAUTIONS FOR USE

1. Applying stress that exceeds the absolute maximum rating

If the voltage or current value for any of the terminals exceeds the absolute maximum rating, internal elements will deteriorate because of the excessive voltage or current. In extreme cases, wiring may melt, or silicon P/N junctions may be destroyed.

As a result, the design should ensure that the absolute maximum ratings will never be exceeded, even momentarily. (Use at 15V DC or lower and 9V AC or lower is recommended.)

2. Deterioration and destruction caused by discharge of static electricity

This phenomenon is generally called static electricity destruction. This occurs when static electricity generated by various factors is discharged while the relay terminals are in contact. The result can produce internal destruction of the element.

To prevent problems from static electricity, the following precautions and measures should be taken when using your device.

1) Employees handling relays should

wear anti-static clothing and should be grounded through protective resistance of 500 kΩ to 1 MΩ.

2) A conductive metal sheet should be placed over the work table. Measuring instruments and jigs should be grounded.

3) When using soldering irons, either use irons with low leakage current, or ground the tip of the soldering iron. (Use of low-voltage soldering irons is also recommended.)

4) Devices and equipment used in assembly should also be grounded.

5) When packing printed circuit boards and equipment, avoid using high-polymer materials such as foam styrene, plastic, and other materials which carry an electrostatic charge.

6) When storing or transporting relays, the environment should not be conducive to generating static electricity (for instance, the humidity should be between 45 and 60%). Relay should always be protected by using non-conductive packing materials.


3. Short across terminals

Do not short circuit between terminals when relay is energized. There is

possibility of breaking the internal IC.

4. Surge voltages at the input

If reverse surge voltages are present at the input terminals, connect a diode in reverse parallel across the input terminals and keep the reverse voltages below the reverse breakdown voltage.




5. Recommended LED forward current (I_F)

It is recommended that the LED forward current (I_F) be kept at 5mA.

6. Ripple in the input power supply

If ripple is present in the input power supply, observe the following:


- 1) For LED operate current at E_{min}, maintain the min. 5mA.
- 2) Keep the LED operate current at 50 mA or less at E_{max}.



7. Output spike voltages

1) In the case of inductive load, suppress voltage spikes occurring in the load to no more than the absolute maximum rated load voltage.

Typical circuits are shown below.



2) If spike voltages generated at the load are limited with a clamp diode or CR snubber circuit and the circuit wires are long, spike voltages will occur by inductance. Keep wires as short as possible to minimize inductance.

8. Cleaning solvents compatibility


Dip cleaning with an organic solvent is recommended for removal of solder flux, dust, etc. Select a cleaning solvent from the following table. If ultrasonic cleaning is used, the severity of factors such as frequency, output power and cleaning solvent selected may cause loose wires and other defects. Make sure these conditions are correct before use. For details, please consult us.

Cleaning solvent		Compatibility (○: Yes X: No)
Chlorine base	• Trichlene • Chloroethylene	○
Aqueous	• Indusco • Hollis • Lonco Terg	○
Alcohol base	• IPA • Ethanol	○
Others	• Thinner • Gasoline	X

9. Soldering


When soldering this terminals, the following conditions are recommended.

(1) IR (Infrared reflow) soldering method




T₁ = 155 to 165°C 311 to 329°F
 T₂ = 180°C 200°C 356 to 392°F
 T₃ = 245°C 473°F or less
 t₁ = 120 s or less
 t₂ = 30 s or less

(2) Vapor phase soldering method



T₁ = 180 to 200°C 366 to 392°F
 T₂ = 215°C 419°F or less
 t₁ = 40 s
 t₂ = 40 s or less

(3) Double wave soldering method



T₁ = 155 to 165°C 311 to 329°F
 T₂ = 260°C 500°F or less
 t₁ = 60 s or less
 t₂+t₃ = 5 s or less

(4) Soldering iron method

Tip temperature: 280 to 300°C 536 to 572°F

Wattage: 30 to 60 W

Soldering time: within 5 s

(5) Others

Check mounting conditions before using other soldering methods (hot-air, hot plate, pulse heater, etc.)

• The temperature profile indicates the temperature of the soldered terminal on the surface of the PC board. The ambient


temperature may increase excessively. Check the temperature under mounting conditions.

• The conditions for the infrared reflow soldering apply when preheating using the VPS method.

10. The following shows the packaging format

1) Tape and reel

mm inch



AQY2

2) Storage

PhotoMOS relays implemented in SSOP types are sensitive to moisture and come in sealed moisture-proof packages.

Observe the following cautions on storage.

- After the moisture-proof package is unsealed, take the devices out of storage as soon as possible (within 1 month at the most).
- If the devices are to be left in storage for a considerable period after the moisture-proof package has been unsealed, it is recommended to keep them in another moisture-proof bag containing silica gel (within 3 months at the most).

When heat stress is applied during solder mounting under conditions of humidity absorption, the moisture

vaporizes and expands, which could increase package-internal responsiveness and cause cracking on the package surface. For this reason, be sure to stay within the solder parameters of item 9.

11. Transportation and storage

1) Extreme vibration during transport will warp the lead or damage the relay.

Handle the outer and inner boxes with care.

2) Storage under extreme conditions will cause soldering degradation, external appearance defects, and deterioration of the characteristics. The following storage conditions are recommended:

- Temperature: 0 to 45°C **32 to 113°F**
- Humidity: Less than 70% R.H.
- Atmosphere: No harmful gasses such as sulfuric acid gas, minimal dust.

12. Notes for mounting

1) If many different packages are combined on a single substrate, then lead temperature rise is highly dependent on package size. For this reason, please make sure that the temperature of the terminal solder area of the PhotoMOS relay falls within the temperature conditions of item 9 before mounting.

2) If the mounting conditions exceed the recommended solder conditions in item 9, resin strength will fall and the nonconformity of the heat expansion coefficient of each constituent material will increase markedly, possibly causing cracks in the package, severed bonding wires, and the like. For this reason, please inquire with us about whether this use is possible.

These materials are printed on ECF pulp.
These materials are printed with earth-friendly vegetable-based (soybean oil) ink.



Please contact

Matsushita Electric Works, Ltd.

Automation Controls Company

■ Head Office: 1048, Kadoma, Kadoma-shi, Osaka 571-8686, Japan

■ Telephone: Japan (81) Osaka (06) 6908-1050

■ Facsimile: Japan (81) Osaka (06) 6908-5781

<http://www.nais-e.com/>

COPYRIGHT © 2003 All Rights Reserved