

### Description

- For 5mm x 20mm fuses
- Tin-plated brass terminals
- Shock safety of PC2
- High temperature Thermoplastic meets:
  - UL 94 VO
  - Glow wire test: 960°C IEC 695-2-1
- Designed to IEC 68-2-20

### Agency Information

- UL Recognized: IZLT2, E14853A
- CSA Component Certified: Class 6225-01, File 47235



### Ordering

- Specify packaging and product code


### SPECIFICATIONS

Product Code	Cap Type	Voltage Rating AC	Current Rating AC	Ambient Temperature	Temperature Rise	Maximum Temperature (C)
HTC-35M	Threaded Cap/Carrier	250V	6.3A	24C	43C	75
HTC-40M	Screwdriver Slot	250V	6.3A	24C	43C	75
HTC-55M	Bayonet Cap/Carrier	250V	6.3A	24C	43C	65
HTC-70M	Bayonet Cap/Carrier	250V	10A	24C	43C	65


### Dimensions

Drawing Not to Scale


#### HTC-35M




#### HTC-55M



#### HTC-40M



#### HTC-70M



Component	Material
Terminal	Tin-Plated Brass
Body	Thermoplastic
Cap	Thermoplastic
Nut	Polycarbonate

### PACKAGING CODE

Packaging Code	Description
Blank	10 pieces of fuseholders packed into a carton
BK	100 pieces of fuseholders packed into a cardboard shelf package

#### North America

Cooper Electronic Technologies  
1225 Broken Sound Parkway NW  
Suite F  
Boca Raton, FL 33487-3533  
Tel: 1-561-998-4100  
Fax: 1-561-241-6640  
Toll Free: 1-888-414-2645

Cooper Bussmann  
P.O. Box 14460  
St. Louis, MO 63178-4460  
Tel: 1-636-394-2877  
Fax: 1-800-544-2570

#### Europe

Cooper Electronic Technologies  
Cooper (UK) Limited  
Burton-on-the-Wolds  
Leicestershire • LE12 5TH UK  
Tel: +44 (0) 1509 882 737  
Fax: +44 (0) 1509 882 786

Cooper Electronic Technologies  
Avda. Santa Eulalia, 290  
08223  
Terrassa, (Barcelona), Spain  
Tel: +34 937 362 812  
+34 937 362 813  
Fax: +34 937 362 719

#### Asia Pacific

Cooper Electronic Technologies  
1 Jalan Kilang Timor  
#06-01 Pacific Tech Centre  
Singapore 159303  
Tel: +65 278 6151  
Fax: +65 270 4160