


Film, Metallized Polypropylene, DC Link, C4AE, 40 uF, 5%, 600 V, 70C, Lead Spacing = 37.5mm



Dimensions

L	42mm +0.6mm
H	45mm +0.2mm
T	30mm +0.4mm
S	37.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM
G	0.5mm NOM

Packaging Specifications

Packaging:	Bulk, Box
------------	-----------

General Information

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	C4AE
RoHS:	Yes
Termination:	Tin
Lead:	4 Wire Leads
Miscellaneous:	Thermal Resistance = 15 C/W

Specifications

Capacitance:	40 uF
Capacitance Tolerance:	5%
Voltage DC:	600 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Max dVdt:	9 V
Resistance:	2.8 mOhms (10kHz 70C)
Current:	18 Amps (10kHz 70C), 344 Amps (Peak)
Inductance:	30 nH