

## CFR50J18R Product Details



**CFR50J18R**

TE Internal Number: 3-1623932-4

 [Active](#)

### Fixed Resistors

 [Converted to EU RoHS/ELV Compliant](#)  
([Statement of Compliance](#))

#### Product Highlights:

- Fixed Resistor
- Resistor Type = General Purpose Resistor
- Resistance Selection = <1K  $\Omega$
- Resistance = 18  $\Omega$
- Power Rating = .50 W

[View all Features](#)

[Buy Product](#)

Documentation & Additional Information	
<p><b>Product Drawings:</b></p> <ul style="list-style-type: none"> <li>● <a href="#">CARBON FILM FIXED RESISTORS SERIES CFR50</a> (PDF, English)</li> </ul> <p><b>Catalog Pages/Data Sheets:</b></p> <ul style="list-style-type: none"> <li>● <a href="#">Ceramic Film Fixed Resistors - Type CFR Series - Tyc...</a> (PDF, English)</li> </ul> <p><b>Product Specifications:</b></p> <ul style="list-style-type: none"> <li>● None Available</li> </ul> <p><b>Application Specifications:</b></p> <ul style="list-style-type: none"> <li>● None Available</li> </ul> <p><b>Instruction Sheets:</b></p> <ul style="list-style-type: none"> <li>● None Available</li> </ul> <p><b>CAD Files:</b></p> <ul style="list-style-type: none"> <li>● None Available</li> </ul>	<p><b>Additional Information:</b></p> <ul style="list-style-type: none"> <li>● <a href="#">Product Line Information</a></li> </ul> <p><b>Related Products:</b></p> <ul style="list-style-type: none"> <li>● <a href="#">Tooling</a></li> </ul>

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p><b>Product Type Features:</b></p> <ul style="list-style-type: none"> <li>● Product Type = Fixed Resistor</li> <li>● Resistor Type = General Purpose Resistor</li> <li>● <a href="#">Resistance (<math>\Omega</math>)</a> = 18</li> <li>● <a href="#">Element</a> = Carbon Film</li> <li>● <a href="#">Termination Type</a> = Tinned Copper Leads</li> </ul> <p><b>Electrical Characteristics:</b></p> <ul style="list-style-type: none"> <li>● <a href="#">Resistance Selection (<math>\Omega</math>)</a> = &lt;1K</li> <li>● <a href="#">Power Rating (W)</a> = 0.50</li> <li>● <a href="#">Tolerance (%)</a> = 5</li> <li>● <a href="#">Package Type</a> = Ammo Packed</li> </ul> <p><b>Body Related Features:</b></p> <ul style="list-style-type: none"> <li>● <a href="#">Series</a> = CFR50</li> <li>● <a href="#">Mount Style</a> = Axial Leaded</li> <li>● <a href="#">Package, Component Size</a> = 8.5 x 3.5</li> </ul>	<p><b>Industry Standards:</b></p> <ul style="list-style-type: none"> <li>● <a href="#">RoHS/ELV Compliance</a> = RoHS compliant, ELV compliant</li> <li>● <a href="#">Lead Free Solder Processes</a> = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C</li> <li>● RoHS/ELV Compliance History = Converted to comply with RoHS directive</li> </ul> <p><b>Conditions for Usage:</b></p> <ul style="list-style-type: none"> <li>● <a href="#">Temperature Coefficient (ppm/°C)</a> = -1200 to 0</li> </ul> <p><b>Operation/Application:</b></p> <ul style="list-style-type: none"> <li>● <a href="#">Application</a> = Various</li> </ul> <p><b>Other:</b></p> <ul style="list-style-type: none"> <li>● Brand = Neohm</li> </ul>