

Metal Film Resistors, Industrial, Precision



FEATURES

- Small size - conformal coated
- Flame retardant epoxy coating
- Controlled temperature coefficient
- Excellent high frequency characteristics
- Exceptionally low noise; typically 0.10 $\mu\text{V/V}$
- Low voltage coefficient to ± 5 ppm/V
- Compliant to RoHS directive 2002/95/EC
- Special tolerance and or TC matching available on request



RoHS*
COMPLIANT

Vishay Dale Model CMF is also available as Military Qualified Styles RN and RL. See appropriate catalog or web page for the MIL-SPEC ratings/attributes. (Except for marking, the Industrial and Military versions are exactly the same. Depending upon stock, military marked parts may be supplied as industrial rated parts).

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	HISTORICAL MODEL	MAXIMUM WORKING VOLTAGE (1) V	RESISTANCE RANGE Ω									
			0.1 % to 1 %	0.1 % to 0.5 %	1 % to 5 %	1 %	2 %, 5 %	1 %	2 %, 5 %	1 %	2 %, 5 %	
			25 ppm/°C	50 ppm/°C	50 ppm/°C	100 ppm/°C	100 ppm/°C	150 ppm/°C	150 ppm/°C	200 ppm/°C	200 ppm/°C	
CMF50	CMF-50	200	10 to 2.5M	10 to 2.5M	10 to 2.5M	10 to 2.5M	10 to 2.5M	10 to 22M	10 to 22M	10 to 22M	10 to 22M	
CMF55	CMF-55	250	10 to 2.5M	10 to 2.5M	10 to 5M	1 to 22.1M	1 to 22.1M	0.5 to 50M	0.5 to 50M	0.5 to 50M	0.1 to 50M	
CMF60	CMF-60	500	10 to 2.5M	10 to 2.5M	10 to 10M	1 to 10M	1 to 10M	0.5 to 10M	0.5 to 10M	0.5 to 10M	0.1 to 10M	
CMF65	CMF-65	500	10 to 2.5M	10 to 2.5M	10 to 10M	1 to 15M	1 to 15M	0.5 to 22M	0.5 to 22M	0.5 to 22M	0.1 to 22M	
CMF70	CMF-70	500	10 to 2.5M	10 to 2.5M	10 to 10M	1 to 15M	1 to 15M	1 to 22M	1 to 22M	1 to 22M	1 to 22M	
CMF07	CMF-07	250	-	-	-	-	5 to 5M	-	1 to 5M	-	1 to 5M	
CMF20	CMF-20	500	-	-	-	-	5 to 10M	-	1 to 10M	-	1 to 10M	

Note

(1) Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less

MAXIMUM COMMERCIAL POWER RATING

WATTAGE (2)	MODEL						
	CMF50	CMF55	CMF60	CMF65	CMF70	CMF07	CMF20
At + 70 °C	0.25 W	0.5 W	1 W	1 W	1 W	0.5 W	1 W
At + 125 °C	0.125 W	0.25 W	0.5 W	0.75 W	0.75 W	-	-

Note

(2) See the load life shift due to power and derating table for a summary of the more common combinations of power rating, case size and ambient operating temperature that prevail in various industrial and military resistor specifications. The "performance" table qualifies the load life stability under these combinations.


GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: CMF55301R00FKRE (preferred part numbering format)



GLOBAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMPERATURE COEFFICIENT (3)	PACKAGING	SPECIAL
(See Standard Electrical Specifications table)	R = Ω K = k Ω M = M Ω R10000 = 0.1 Ω 680K00 = 680 k Ω 1M0000 = 1.0 M Ω	B = ± 0.1 % C = ± 0.25 % D = ± 0.5 % F = ± 1 % G = ± 2 % J = ± 5 %	E = 25 ppm H = 50 ppm K = 100 ppm L = 150 ppm N = 200 ppm	EK = Lead (Pb)-free, bulk EA = Lead (Pb)-free, T/R (full) EB = Lead (Pb)-free, T/R (1000 pieces) BF = Tin/lead, bulk RE = Tin/lead, T/R (full) R6 = Tin/lead, T/R (1000 pieces)	Blank = Standard (Dash Number) (Up to 3 digits) From 1 to 999 as applicable 70 = Color banded, 5 bands (≤ 1 %) 80 = Color banded, 4 bands (≥ 2 %)

Historical Part Number example: CMF-553010FT-1 (will continue to be accepted)




Note

(3) Tolerances of ± 0.5 % (D), ± 0.25 % (C) and ± 0.1 % (B) are available only in 50 ppm and 25 ppm temperature coefficients

* Pb containing terminations are not RoHS compliant, exemptions may apply

DIMENSIONS in inches (millimeters)



GLOBAL MODEL	A	B	C (Max.)	D
CMF50	0.150 ± 0.020 (3.81 ± 0.51)	0.065 ± 0.015 (1.65 ± 0.38)	0.187 (4.75)	0.016 ± 0.002 (0.41 ± 0.05)
CMF55	0.240 ± 0.020 ⁽⁴⁾ (6.10 ± 0.51)	0.090 ± 0.008 (2.29 ± 0.20)	0.278 (7.06) ⁽³⁾	0.025 ± 0.002 (0.64 ± 0.05)
CMF60	0.344 ± 0.031 (8.74 ± 0.79)	0.145 ± 0.015 (3.68 ± 0.38)	0.425 (10.80)	0.025 ± 0.002 ⁽²⁾ (0.64 ± 0.05)
CMF65	0.562 ± 0.031 (14.27 ± 0.79)	0.180 ± 0.015 (4.57 ± 0.38)	0.687 (17.45)	0.025 ± 0.002 (0.64 ± 0.05)
CMF70	0.562 ± 0.031 (14.27 ± 0.79)	0.180 ± 0.015 (4.57 ± 0.38)	0.687 (17.45)	0.032 ± 0.002 (0.81 ± 0.05)
CMF07	0.240 ± 0.020 (6.10 ± 0.51)	0.090 ± 0.008 (2.29 ± 0.20)	0.278 (7.06)	0.025 ± 0.002 (0.64 ± 0.05)
CMF20	0.375 ± 0.040 (9.53 ± 1.02)	0.145 ± 0.015 (3.68 ± 0.38)	0.425 (10.80)	0.032 ± 0.002 (0.81 ± 0.05)

Notes

- (1) 1.08" ± 0.125" (27.43 mm ± 3.18 mm) if tape and reel
- (2) Available with 0.032" (0.813 mm) lead [CMF60..95]
- (3) 0.290" (7.37 mm) for ± 0.25 % and ± 0.1 % resistance tolerances and values > 1 MΩ
- (4) 0.260" ± 0.020" (6.60 mm ± 0.51 mm) for values > 5 MΩ

TECHNICAL SPECIFICATIONS								
PARAMETER	UNIT	CMF50	CMF55	CMF07	CMF60	CMF20	CMF65	CMF70
Maximum Working Voltage	V _≐	≤ 200	≤ 250	≤ 250	≤ 500	≤ 500	≤ 500	≤ 500
Insulation Voltage (1 Min)	V _{eff}	> 500						
Voltage Coefficient (Max.)	ppm/V	± 5 (measured between 10 % and full rated voltage)						
Dielectric Strength	V _{AC}	450	450	450	750	750	900	900
Insulation Resistance	Ω	≥ 10 ¹¹						
Operating Temperature Range	°C	- 55 to + 175						
Terminal Strength (Pull Test)	lb	2	2	5	2	5	2	5
Noise	dB	0.10 μV/V over a decade of frequency, with low and intermediate resistance values typically below 0.5 μV/V						
Weight (Max.)	g	0.12	0.20	0.20	0.50	0.60	1.00	1.10



TEMPERATURE COEFFICIENT CODES		
GLOBAL TC CODE	HISTORICAL TC CODE	TEMPERATURE COEFFICIENT
E	T-9	25 ppm/°C
H	T-2	50 ppm/°C
K	T-1	100 ppm/°C
L	T-0	150 ppm/°C
N	T-00	200 ppm/°C

LOAD LIFE SHIFT DUE TO POWER AND DERATING (AT 70 °C AND AT + 125 °C)

The power rating for the CMF parts is tied to the derating temperature, the heat rise of the parts, and the ΔR for the load life performance. When the tables/graphs below are used together they show that when the parts are run at their higher power ratings, the parts will run hotter, which has the potential of causing the resistance of the parts to shift more over the life of the part.

LOAD LIFE SHIFT VS. POWER RATING						
LOAD LIFE	MAXIMUM ΔR (TYPICAL TEST LOTS)					
	± 0.15 %	± 0.5 %	± 1.0 %	± 0.15 %	± 0.5 %	± 1.0 %
MODEL	POWER RATING AT + 70 °C			POWER RATING AT + 125 °C		
CMF50	1/20 W and 1/10 W	1/8 W	1/4 W	1/20 W	1/10 W	1/8 W
CMF55, CMF07	1/10 W and 1/8 W	1/4 W	1/2 W	1/10 W	1/8 W	1/4 W
CMF60, CMF20	1/8 W and 1/4 W	1/2 W	3/4 W and 1 W	1/8 W	1/4 W	1/2 W
CMF65	1/4 W and 1/2 W	3/4 W	1 W	1/4 W	1/2 W	3/4 W
CMF70	1/4 W and 1/2 W	3/4 W	1 W	1/4 W	1/2 W	3/4 W

CMF resistors have an operating temperature range of - 55 °C to + 175 °C. They must be derated at high ambient temperatures according to the derating curve.



DERATING

Example:

When a CMF55 part is run at 1/8 W in a 70 °C ambient environment, the resistor will generate enough heat that the surface temperature of the part will reach about 19 °C over the ambient temperature, and over the life of the part this could cause the resistance value to shift up to ± 0.15 %.

If the same resistor was instead run at 1/4 W in a 70 °C environment, the element will heat up to about 30 °C over ambient, and over the life of the part the resistance value could shift roughly ± 0.5 %.

And if the resistor was run at its maximum power rating of 1/2 W in a 70 °C environment, it will heat up to about 58 °C over ambient, and you could see the resistance value shift roughly ± 1 % over the life of the part.

MATERIAL SPECIFICATIONS

Element:	Vacuum-deposited nickel-chrome alloy	Coating:	Flame retardant epoxy, formulated for superior moisture protection
Core:	Fire-cleaned high purity ceramic	Solderability:	Continuous satisfactory coverage when tested in accordance with MIL-R-10509



SPECIAL MODIFICATIONS

1. Terminals may be supplied in any commercial material with several type finishes.
2. Special pre-conditioning (power aging, temperature cycling, etc.) to customer specifications.
3. Non-helixed resistors can be supplied for critical high frequency applications.
4. Fusible, flameproof versions available.

MARKING
<ul style="list-style-type: none"> - Value - Decade and tolerance - Date code <p>(Alternately, parts may be MIL marked)</p>

Note

- CMF07 and CMF20 parts are marked with color bands, either per MIL-PRF-22684 (with a wide white band) or using commercial color bands. CMFxx..70 and CMFxx..80 parts are marked using commercial color bands.

PERFORMANCE		
TEST (TEST METHODS - MIL-STD-202)	AT + 70 °C	AT + 125 °C
	MAXIMUM ΔR (TYPICAL TEST LOTS)	
Short Time Overload	± 0.05 %	± 0.05 %
Low Temperature Operation	± 0.05 %	± 0.05 %
Moisture Resistance	± 0.05 %	± 0.05 %
Shock	± 0.01 %	± 0.01 %
Vibration	± 0.004 %	± 0.04 %
Temperature Cycling	± 0.15 %	± 0.15 %
Load Life	Varies based on power rating used; see load life shift due to power and derating table	
Dielectric Withstanding Voltage	± 0.01 %	± 0.01 %
Effect of Solder	± 0.03 %	± 0.03 %



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.