

- Features:
- ✓ General purpose resistor ideal for commercial/industrial applications
  - ✓ Flame retardant coatings standard
  - ✓ Flameproof version available as CFF
  - ✓ Panasert available on selected sizes; contact factory
  - ✓ Auto sequencing/insertion compatible
  - ✓ CFM (mini) ideal choice when size constraints apply
  - ✓ Cut and formed product is available on select sizes; contact factory
  - ✓ Standard lead wire for CF/CFM is copper plated steel, with 100% tin over plate
  - ✓ 100% tin plate on copper wire is available as type CFQ/CFQM
  - ✓ RoHS compliant / lead-free




Electrical Specifications						
Type / Code	Power Rating (Watts) @ 70°C	Maximum Working Voltage ①	Maximum Overload Voltage	Dielectric Withstanding Voltage	Ohmic Range and Tolerance	
					2%	5%
CF 1/8	0.125W	250V	500V	350V	10Ω - 1MΩ	1Ω - 22MΩ
CF 1/4	0.250W	350V	600V	350V	1Ω - 1MΩ	1Ω - 22MΩ
CF 1/2	0.500W	350V	700V	600V	10Ω - 1MΩ	1Ω - 10MΩ
CF 1	1.000W	500V	1,000V	600V	1Ω - 1MΩ	1Ω - 10MΩ
CF 2	2.000W	500V	1,000V	600V	10Ω - 1MΩ	1Ω - 10MΩ
CFM 1/4	0.250W	250V	500V	350V	10Ω - 1MΩ	1Ω - 10MΩ
CFM 1/2	0.500W	350V	600V	350V	10Ω - 1MΩ	1Ω - 10MΩ

① Lesser of  $\sqrt{PR}$  or maximum working voltage.

### How to Order

SEI Type		Code	Nominal Resistance	Tolerance	Packaging					
CF		1/2	100K	5%	R					
Code	Description	Code	Wattage	Tolerance	SEI Types	R	A	T	P	Q
CF	Standard	1/8	0.125W	2%	CF 1/8 CF 1/4 CF 1/2	Tape & Reel	Bulk	Tape & Box (Ammo Box)	Panasert & Reel	Panasert & Box (Ammo Box)
CFF	Flameproof	1/4	0.250W	5%						
CFM	Mini	1/2	0.500W		CF 1	2,000	1,000	1,000	N/A	N/A
PCF	Panasert CF 1/4	1	1.000W		CF 2	1,000		1,000		
PCFM	Panasert CF 1/2	2	2.000W		CFM 1/4	5,000		5,000		
CFQ	Tin plating on copper wire				CFM 1/2					
CFQM	Tin plating (mini)				PCF 1/4	N/A			5,000	2,000
					PCFM 1/2	N/A				



Mechanical Specifications					
Type / Code	A Body Length	B Body Diameter	C Lead Length(Bulk)	D Lead Diameter	Units
CF 1/8	0.13 ± 0.01	0.07 ± 0.01	1.10 ± 0.12	0.018 ± 0.003	inches
	3.3 ± 0.3	1.7 ± 0.3	28 ± 3	0.45 ± 0.08	mm
CF 1/4	0.26 ± 0.02	0.09 ± 0.01	1.10 ± 0.12	0.022 ± 0.003	inches
	6.5 ± 0.05	2.3 ± 0.3	28 ± 3	0.55 ± 0.08	mm
CF 1/2	0.33 ± 0.04	0.11 ± 0.02	1.18 ± 0.12	0.022 ± 0.002	inches
	8.5 ± 1	2.7 ± 0.5	30.0 ± 3	0.56 ± 0.05	mm
CF 1	0.43 ± 0.04	0.18 ± 0.02	1.18 ± 0.12	0.028 ± 0.004	inches
	11.0 ± 1	4.5 ± 0.5	30.0 ± 3	0.70 ± 0.1	inches
CFM 1/4	0.13 ± 0.01	0.07 ± 0.01	1.10 ± 0.12	0.018 ± 0.003	inches
	3.3 ± 0.3	1.7 ± 0.3	28 ± 3	0.45 ± 0.08	mm
CFM 1/2	0.26 ± 0.04	0.09 ± 0.01	1.10 ± 0.12	0.022 ± 0.003	inches
	6.5 ± 1	2.3 ± 0.3	28 ± 3	0.55 ± 0.08	mm

Performance Characteristics		
Test	Standard / Method	Test Results
Short Time Overload	EIA-RS-172-B 3.2.6	± 0.5%
Resistance to Solder Heat	MIL-STD 202 Method 210	± 0.5%
Dielectric Withstanding Voltage	JIS C 5202 5.6	± 0.5%
Load Life	MIL-STD 202 Method 108	± 1%
Terminal Strength	MIL-STD 202 Method 211	± 0.2%
Moisture Resistance	MIL-STD 202 Method 106	± 0.5%

Operating Temperature Range: -55°C to +155°C