

## Dual N-Channel NexFET™ Power MOSFET

 Check for Samples: [CSD86311W1723](#)

### FEATURES



- Dual N-Ch MOSFETs
- Common Source Configuration
- Small Footprint 1.7 mm × 2.3 mm
- Ultra Low  $Q_g$  and  $Q_{gd}$
- Pb Free
- RoHS Compliant
- Halogen Free

### APPLICATIONS

- Battery Management
- Battery Protection
- DC-DC Converters

### DESCRIPTION

The device has been designed to deliver the lowest on resistance and gate charge in the smallest outline possible with thermal characteristics in an ultra low profile. Low on resistance and gate charge coupled with the small footprint and low profile make the device ideal for battery operated space constrained application in load management as well as DC-DC converter applications

**Top View**

 **$R_{DS(on)}$  vs  $V_{GS}$** 


### PRODUCT SUMMARY

$V_{DS}$	Drain to Source Voltage	25	V
$Q_g$	Gate Charge Total (4.5V)	3.1	nC
$Q_{gd}$	Gate Charge Gate to Drain	0.33	nC
$R_{DS(on)}$	Drain to Source On Resistance	$V_{GS} = 2.5V$	37 mΩ
		$V_{GS} = 4.5V$	31 mΩ
		$V_{GS} = 8V$	29 mΩ
$V_{GS(th)}$	Threshold Voltage	1	V


### ORDERING INFORMATION

Device	Package	Media	Qty	Ship
CSD86311W1723	1.7-mm × 2.3-mm Wafer Level Package	7-inch reel	3000	Tape and Reel

### ABSOLUTE MAXIMUM RATINGS

$T_A = 25^\circ\text{C}$ unless otherwise stated		VALUE	UNIT
$V_{DS}$	Drain to Source Voltage	25	V
$V_{GS}$	Gate to Source Voltage	+10 / -8	V
$I_D$	Continuous Drain Current <sup>(1)</sup> <sup>(2)(3)</sup>	4.5	A
	Pulsed Drain Current <sup>(1)</sup> <sup>(2)(3)</sup>		
$I_G$	Continuous Gate Clamp Current <sup>(4)</sup>	6	A
	Pulsed Gate Clamp Current <sup>(4)</sup>		
$P_D$	Power Dissipation <sup>(1)</sup>	1.5	W
$T_J, T_{STG}$	Operating Junction and Storage Temperature Range	-55 to 150	$^\circ\text{C}$

- (1) May be limited by Max source current
- (2) Based on Min Cu footprint
- (3) Per MOSFET
- (4) Total for device

 **$R_{D1D2(on)}$  vs  $V_{GS}$** 


Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## ELECTRICAL CHARACTERISTICS

( $T_A = 25^\circ\text{C}$  unless otherwise stated)


PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
<b>Static Characteristics</b>						
$BV_{DSS}$	Drain to Source Voltage	$V_{GS} = 0V, I_D = 250\mu A$	25			V
$I_{DSS}$	Drain to Source Leakage Current	$V_{GS} = 0V, V_{DS} = 20V$			1	$\mu A$
$I_{GSS}$	Gate to Source Leakage Current	$V_{DS} = 0V, V_{GS} = +10 / -8V$			$\pm 100$	nA
$V_{GS(th)}$	Gate to Source Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250\mu A$	0.85	1	1.4	V
$R_{DS(on)}$	Drain to Source On Resistance	$V_{GS} = 2.5V, I_{DS} = 2A$		37	51	m $\Omega$
		$V_{GS} = 4.5V, I_{DS} = 2A$		31	42	m $\Omega$
		$V_{GS} = 8V, I_{DS} = 2A$		29	39	m $\Omega$
$R_{DD(on)}$	Drain to Drain On Resistance	$V_{GS} = 2.5V, I_D = 2A$		52	75	m $\Omega$
		$V_{GS} = 4.5V, I_{DS} = 2A$		41	55	m $\Omega$
		$V_{GS} = 8V, I_{DS} = 2A$		38	50	m $\Omega$
$g_{fs}$	Transconductance	$V_{DS} = 10V, I_D = 2A$		6.4		S
<b>Dynamic Characteristics</b>						
$C_{ISS}$	Input Capacitance	$V_{GS} = 0V,$ $V_{DS} = 12.5V,$ $f = 1MHz$		450	585	pF
$C_{OSS}$	Output Capacitance			250	325	pF
$C_{RSS}$	Reverse Transfer Capacitance			10	13	pF
$R_G$	Series Gate Resistance			1.4	2.8	$\Omega$
$Q_g$	Gate Charge Total (4.5V)	$V_{DS} = 12.5V,$ $I_D = 2A$		3.1	4	nC
$Q_{gd}$	Gate Charge Gate to Drain			0.33		nC
$Q_{gs}$	Gate Charge Gate to Source			0.85		nC
$Q_{g(th)}$	Gate Charge at $V_{th}$			0.48		nC
$Q_{OSS}$	Output Charge	$V_{DS} = 12.2V, V_{GS} = 0V$		4.5		nC
$t_{d(on)}$	Turn On Delay Time	$V_{DS} = 12.5V, V_{GS} = 4.5V,$ $I_D = 2A, R_G = 2\Omega$		5.4		ns
$t_r$	Rise Time			4.3		ns
$t_{d(off)}$	Turn Off Delay Time			13.2		ns
$t_f$	Fall Time			2.9		ns
<b>Diode Characteristics</b>						
$V_{SD}$	Diode Forward Voltage	$I_S = 2A, V_{GS} = 0V$		0.78	1	V
$Q_{rr}$	Reverse Recovery Charge	$V_{dd} = 12.2V, I_F = 2A,$ $di/dt = 300A/\mu s$		4.2		nC
$t_{rr}$	Reverse Recovery Time			13.4		ns

## THERMAL CHARACTERISTICS

( $T_A = 25^\circ\text{C}$  unless otherwise stated)


PARAMETER		MIN	TYP	MAX	UNIT
$R_{\theta JA}$	Thermal Resistance Junction to Ambient (Minimum Cu area) <sup>(1)</sup> <sup>(2)</sup>			165	$^\circ\text{C}/\text{W}$
$R_{\theta JA}$	Thermal Resistance Junction to Ambient (1 in <sup>2</sup> Cu area) <sup>(2)</sup> <sup>(3)</sup>			68	$^\circ\text{C}/\text{W}$

- (1) Device mounted on FR4 material with minimum Cu mounting area.
- (2) Measured with both devices biased in a parallel condition.
- (3) Device mounted on FR4 material with 1 in<sup>2</sup> of 2oz. Cu.



M0182-01

Max  $R_{\theta JA} = 68^{\circ}\text{C/W}$   
when mounted on  
1inch<sup>2</sup> of 2 oz. Cu.




M0183-01

Max  $R_{\theta JA} = 165^{\circ}\text{C/W}$   
when mounted on  
minimum pad area of 2  
oz. Cu.

### TYPICAL MOSFET CHARACTERISTICS

( $T_A = 25^{\circ}\text{C}$  unless otherwise stated)




G012


Figure 1. Transient Thermal Impedance

**TYPICAL MOSFET CHARACTERISTICS (continued)**


( $T_A = 25^\circ\text{C}$  unless otherwise stated)




**Figure 2. Saturation Characteristics**




**Figure 3. Transfer Characteristics**




**Figure 4. Gate Charge**



**Figure 5. Capacitance**




**Figure 6. Threshold Voltage vs. Temperature**




**Figure 7.  $R_{DS(on)}$  vs. Gate-to-Source Voltage**

**TYPICAL MOSFET CHARACTERISTICS (continued)**


( $T_A = 25^\circ\text{C}$  unless otherwise stated)




**Figure 8.  $R_{D1D2(on)}$  vs. Gate-to-Source Voltage**




**Figure 9. On Resistance vs. Temperature**



**Figure 10. Typical Diode Forward Voltage**






**Figure 11. Maximum Safe Operating Area**



**Figure 12. Maximum Drain Current vs. Temperature**

**MECHANICAL DATA**

**CSD86311W1723 Package Dimensions**




Pinout	
Position	Designation
A2, A3, A4	Drain 1
C2, C3, C4	Drain 2
A1	Gate 1
C1	Gate 2
B1, B2, B3, B4	Source

NOTE: All dimensions are in mm (unless otherwise specified)


M0184-01

### Land Pattern Recommendation



NOTE: All dimensions are in mm (unless otherwise specified)

### Tape and Reel Information



NOTE: All dimensions are in mm (unless otherwise specified)

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Applications Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Automotive and Transportation	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

### TI E2E Community

[e2e.ti.com](http://e2e.ti.com)