

(1.27 mm) .050"

FTS SERIES

MICRO LOW PROFILE TERMINAL STRIPS

SPECIFICATIONS


For complete specifications and recommended PCB layouts see www.samtec.com?FTS

HI-TEMP

Insulator Material:
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Operating Temp Range:
-55°C to +125°C
Plating:
Sn or Au over 50µ" (1.27 µm) Ni
Current Rating:
3.3 A per pin (1 pin powered per row)
RoHS Compliant:
Yes
Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
.004" (0.10 mm) max

Mates with:
FFSD, CLP, FLE

OPTIONS



Mates with socket strips or IDC cable

Surface mount or through-hole

Micro pitch .050" x .050" (1.27 mm x 1.27 mm)

Low profile (1.27 mm) .050"

Shrouded and alignment pin options available

Impedance matched for high speed applications

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)

- Alignment pin
- Contact Samtec.

FTS	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
		02 thru 50 (except -S & -SA option = 05 thru 46)	<p>-01 = .120" (3.05 mm) Post (Mates with FFSD)</p> <p>-02 = .075" (1.91 mm) Post (Mates with FLE)</p> <p>-03 = .065" (1.65 mm) Post (Mates with CLP)</p>	<p>-F = Gold flash on post, Matte Tin on tail</p> <p>-L = 10µ" (0.25 µm) Gold on post, Matte Tin on tail</p>	<p>-D = Double Through-hole</p> <p>-DV = Double Vertical SMT</p> <p>-S = Single Through-hole</p> <p>-SV = Single Vertical SMT</p>	<p>(-D & -DV only)</p> <p>-SA = End Shroud with Alignment Pin (05 thru 46 positions. Style -02 & -03 only)</p> <p>-S = End Shroud (05 thru 46 positions. Style -02 & -03 only)</p> <p>-P = Pick & Place Pad (04 positions minimum)</p> <p>-TR = Tape & Reel (-DV only) (Required callout for positions 2 thru 4)</p>

LEAD STYLE	A
-01	(3.05) .120
-02	(1.91) .075
-03	(1.65) .065

Note: Some lengths, styles and options are non-standard, non-returnable.